

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



String combiner box for photovoltaic systems up to 1,000 V DC for connecting 2x 2 strings. String entry from above. With surge protection (type 1/2), 2x DC switch disconnecter, and SUNCLIX DC connectors for the input and output side (SUNCLIX mating connectors supplied as standard).

Product description

The Solarline string combiner boxes (SCBs) are used in both small rooftop systems and large ground-mounted systems. The main tasks of the SCBs are the surge protection of the photovoltaic system, collecting strings (if necessary), and looping through the protective equipotential bonding conductor for the local equipotential bonding.

Further functions are optional and depend on the equipment.

Examples of optional functions include protecting the strings with string fuses and disconnecting the strings via DC switch disconnectors or DC fire department switches.

You can determine the full scope of functions of the SCB from its item designation (see the application note for the type key of the SCB, which can be downloaded in the "Downloads" area).

Your advantages

- Fast installation and startup
- Standard-compliant switchgear and controlgear assembly, thanks to use of DIN EN 61439
- Application-oriented consultation
- Large portfolio of string combiner boxes in stock

Commercial data

Item number	1140111
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	DTHTBA
GTIN	4063151088545
Weight per piece (including packing)	4.1 kg
Weight per piece (excluding packing)	4.1 kg
Customs tariff number	85363030
Country of origin	DE

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

Technical data

Product properties

Product type	String combiner box (SCB)
Scope of delivery	SUNCLIX DC connector for connecting the SCB
Design	DC switch disconnecter

Insulation characteristics

Protection class	II
------------------	----

Electrical properties

General

MPP voltage U_n	max. 1000 V DC
Non-load voltage U_{OC}	max. 1100 V DC
Current per string I_{max}	max. 16 A
Total current MPP tracker	max. 32 A

DC switch disconnecter

Rated operating current DC-21B	32 A
Rated operating current DC-PV1	32 A
Rated operating current DC-PV2	32 A

Surge protection

EN type	T1
IEC test classification	T1
Protection level U_p	≤ 3.5 kV
Total discharge current I_{total} (10/350) μs	5 kA
Total discharge current I_{total} (8/20) μs	40 kA
Short-circuit current rating I_{SCPV}	32 A

Input data

DC

Number of inputs: Strings	2 (Per MPP tracker)
Number of supported MPP trackers	2

Output data

DC

Number of outputs: MPP tracker	2
Number of outputs: $\pm$	1 (Per MPP tracker)

Connection data

DC input

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

Type of cable entry	SUNCLIX
Cable cross-section range:	2.5 mm² ... 6 mm²

Protective bonding and protective grounding conductor

Type of cable entry	Cable gland
Connection method	Screw connection
Cable cross-section range:	2x 16 mm²
External cable diameter	2x 6 mm ... 12 mm

DC output

Type of cable entry	SUNCLIX
Cable cross-section range:	2.5 mm² ... 6 mm²

Dimensions

Housing

Width	361 mm
Height	254 mm
Depth	111 mm

Material specifications

Material Housing	Polycarbonate
Material Cover/door	Polycarbonate (transparent)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 45 °C

Standards and regulations

Standard designation	Low-voltage switchgear and controlgear assemblies - Part 2: Power switchgear and controlgear assemblies
Standards/specifications	EN 61439-2

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)




1140111

<https://www.phoenixcontact.com/in/products/1140111>

Drawings

Connection diagram




Schematic application drawing

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)

1140111


<https://www.phoenixcontact.com/in/products/1140111>

Dimensional drawing



Housing dimensions

Schematic diagram




Connection of the remote indication contact on the surge protection

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)


1140111

<https://www.phoenixcontact.com/in/products/1140111>

Schematic diagram




IN+




IN-

Connection of the PV strings

Schematic diagram



OUT+



OUT-

Connection to the inverter


SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

Schematic diagram





Connection of the protective grounding conductor

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)

1140111

<https://www.phoenixcontact.com/in/products/1140111>

Schematic diagram



Connection of the protective equipotential bonding conductor

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111
<https://www.phoenixcontact.com/in/products/1140111>

Classifications

ECLASS

ECLASS-13.0	27171490
ECLASS-11.0	27142422

ETIM

ETIM 9.0	EC003857
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

Accessories

PV-C PROTECTION CAP - Protective cap

1785430

<https://www.phoenixcontact.com/in/products/1785430>

Protective cap, Range of articles: SUNCLIX, color: black, self-sealing, without interlock, set consisting of: 1 protective cap for connector side and 1 protective cap for coupling side



VAL-MS-T1/T2 1000DC-PV-ST - Type 1/2 surge protection plug

2801162

<https://www.phoenixcontact.com/in/products/2801162>

Replacement plug for PV arrester combinations from the VAL-MS-T1/T2 1000DC-PV-... product range



SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

PV-C4F-S 6-16 (+) - Connector

1284634

<https://www.phoenixcontact.com/in/products/1284634>



Connector, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 6 mm², max. conductor cross section: 16 mm², rated voltage: 1500 V DC, rated current: 60 A, Connection method: Spring-cage, Contact connection type: Socket, min. cable diameter: 5.5 mm, max. cable diameter: 10 mm

PV-C4M-S 6-16 (-) - Connector

1284632

<https://www.phoenixcontact.com/in/products/1284632>



Connector, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 6 mm², max. conductor cross section: 16 mm², rated voltage: 1500 V DC, rated current: 60 A, Connection method: Spring-cage, Contact connection type: Pin, min. cable diameter: 5.5 mm, max. cable diameter: 10 mm

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

PV-C3F-S 2,5-6 (+) - Photovoltaic connector

1386381

<https://www.phoenixcontact.com/in/products/1386381>



Photovoltaic connector, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 2.5 mm², max. conductor cross section: 6 mm², rated voltage: 1100 V DC, rated current: 35 A, Connection method: Spring-cage, Contact connection type: Socket, min. cable diameter: 5.5 mm, max. cable diameter: 8 mm, Follow-up item to 1774674

PV-ED6/Y-120(2+/1-) - Photovoltaic Y-distributor

1030649

<https://www.phoenixcontact.com/in/products/1030649>



Photovoltaic Y-distributor, Range of articles: SUNCLIX, color: black

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

PV-C3M-S 2,5-6 (-) - Photovoltaic connector

1386384

<https://www.phoenixcontact.com/in/products/1386384>



Photovoltaic connector, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross section: 2.5 mm², max. conductor cross section: 6 mm², rated voltage: 1100 V DC, rated current: 35 A, Connection method: Spring-cage, Contact connection type: Pin, min. cable diameter: 5.5 mm, max. cable diameter: 8 mm, Follow-up item to 1774687

PV-ED6/Y-120(1+/2-) - Photovoltaic Y-distributor

1030650

<https://www.phoenixcontact.com/in/products/1030650>



Photovoltaic Y-distributor, Range of articles: SUNCLIX, color: black

SOL-SC-2ST-0-DC-2MPPT-1101UD - String combiner box (SCB)



1140111

<https://www.phoenixcontact.com/in/products/1140111>

PV-AS-MC4/6-150-MN-SET1 - Photovoltaic adapter set

1079531

<https://www.phoenixcontact.com/in/products/1079531>



Photovoltaic adapter set, Range of articles: SUNCLIX, design: Adapter, color: black, rated current: 35 A, cable length: 150. Connect these connectors only to other connectors of the same type made by the same manufacturer. When making the connections, always observe the specifications regarding nominal voltage and nominal current. The smallest common value is permissible.

TOOL-KIT SOLAR - Tool set

1212071

<https://www.phoenixcontact.com/in/products/1212071>



Tool case, equipped with: crimping pliers, pressing dies for MC3, MC4 and SOLARLOK connectors, stripping tool for commercially available solar cables, stripping tool for SUNCLIX, VDE cable cutter, VDE screwdriver: PH1, PH2, 0.6x3.5 and 0.8x4.0 slots.

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in