

Features

- Tin class V2 according to DIN 40500
- Good solderability
- Uninsulated

RS PRO tin plated Copper Wire Ø 0.5 mm / 0.20mm² 24 AWG, 25m

RS Stock No.: 534-116



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The copper wire from RS has a cross-sectional area of 0.20 mm². It is made of high-quality tinned copper and offers excellent conductivity as well as high corrosion resistance. The wire is suitable for a wide range of electrical and electronic applications and ensures reliable, consistent performance.

General Specifications

| | |
|---------------|--------------------------------|
| Type | Copper Wire |
| Diameter | 0.5 mm |
| Cross-section | AWG 24 (0.20 mm ²) |
| Put-up | Ring at 25m in PE-Foil |

Mechanical Specifications

| | |
|------------------------|---------------------|
| Conductor | Solid tinned copper |
| Material | Electrolytic copper |
| Structure of conductor | Solid wire |
| Surface | tinned |

Approvals

| | |
|---------------|---------------------------------------------------------|
| Compliance | CE, RoHS, REACH |
| Standards Met | Manufactured according to EN 13602 (ETP1) and DIN 46431 |