



Main

Range	Acti9
Product name	Acti9 Isobar A
Product or component type	Loose enclosure
Device application	Distribution
Enclosure mounting	Surface
Door type	Left opening hinged plain door with plastic latch
Provided equipment	DIN rail Door Back plate Enclosure Cover Earth terminal block

Complementary

Number of ways	32 ways (1P)
Number of horizontal rows	2
Enclosure material	Folded sheet steel: RAL 9001 epoxy powder coat
Cable entry	Knock-out 25 mm (top and bottom) Knock-out 25 mm (rear) Knock-out 25 mm (side)
Height	530 Mm
Width	417 Mm
Depth	117 Mm

Environment

IP degree of protection	IP3x
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.000 Cm
Package 1 Width	43.000 Cm
Package 1 Length	54.000 Cm
Package 1 Weight	7.595 Kg
Unit Type of Package 2	P12
Number of Units in Package 2	30

Package 2 Height	107.000 Cm
Package 2 Width	100.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	232.660 Kg

Environmental data

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	174

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**