

Technical data

4T-30212

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	60 mm
D - External diameter	110 mm
B - Bearing/Inner ring width	22 mm
C - Outer ring width	19 mm
T - Total width	23,75 mm
d1 - External diameter inner ring	82 mm
a - Charge load application point	22 mm
rs - Min fillet radius	2 mm
r1s - Min fillet radius	1,5 mm
Mass	0,929 kg
ISO 355 reference	T3EB060

PRODUCT PERFORMANCE

C - Dynamic load	116 kN
C0 - Static load	125 kN
Cu - Fatigue limit load	15,2 kN
A2 - Rating life coefficient	1
e - Coefficient	0.4
Y0 - Static axial load coefficient	0.81
Y2 - Upper axial load coefficient	1.48
N lim - Oil lubrication limit speed	4500 tr/min
N lim - Grease lubrication limit speed	3400 tr/min
Tmin - Min operating temperature	-40 °C



4T-30212

Single row tapered roller bearings

PRODUCT PERFORMANCE

Tmax - Max operating temperature	120 °C
---	--------

ABUTMENT

da max - Max shoulder diameter IR	70 mm
--	-------

db min - Min IR shoulder diameter	70 mm
--	-------

Da min - Min shoulder diameter OR	96 mm
--	-------

Da max - Max shoulder diameter OR	101,5 mm
--	----------

Db min - Min OR shoulder diameter	103 mm
--	--------

Ca - Min clearance	4 mm
---------------------------	------

Cb - Min clearance	4,5 mm
---------------------------	--------

ra max - Max fillet radius	2 mm
-----------------------------------	------

r1a - Max fillet radius	1,5 mm
--------------------------------	--------

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
------------------	---------

Reference	4T-30212
------------------	----------

Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
--------------	---------------------------------

ULTAGE	Non/No
---------------	--------

Rolling element material	Acier de cémentation
---------------------------------	----------------------



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

