

Cover IP40, H: 50 mm W: 600 mm



| Model                                            |               |
|--------------------------------------------------|---------------|
| product brand name                               | SIVACON S4    |
| design of the surface                            | powder-coated |
| net weight                                       | 1.72 kg       |
| height                                           | 50 mm         |
| width                                            | 600 mm        |
| depth                                            | 25 mm         |
| installation width for cabinet installation      | 600 mm        |
| mounting height for device equipment can be used | 50 mm         |
| material                                         | sheet-steel   |
| reference code according to IEC 81346-2          | UC            |

| Approvals Certificates   |       |
|--------------------------|-------|
| General Product Approval | other |

[Miscellaneous](#)



[Miscellaneous](#)

|       |             |
|-------|-------------|
| other | Environment |
|-------|-------------|

[Confirmation](#)

[Environmental Con-  
firmations](#)

[Environmental Con-  
firmations](#)

### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2005-6BA04>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2005-6BA04>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ2005-6BA04](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2005-6BA04)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



