

Eaton 236971

Catalog Number: 236971

Eaton Moeller series xPole - P XK RCBO - residual-current circuit breaker with overcurrent protection. RCBO C 13A 1+N 300mA sensitivity A



General specifications

Product Name	Catalog Number
Eaton Moeller series xPole - P XK RCBO	236971
- residual-current circuit breaker with overcurrent protection	EAN 4015082369712
Product Length/Depth	Product Height
80 mm	75 mm
Product Width	Product Weight
35 mm	0.187 kg
Compliances	Certifications
CE Marked RoHS conform	CE

Product specifications

Type

RCBO

Application

Switchgear for residential and commercial applications

Amperage Rating

13 A

Voltage rating

240 V - 240 V

Surge current capacity

0.25 kA

Voltage type

AC

Width in number of modular spacings

2

Features

Concurrently switching N-neutral

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal

Resources

Declarations of conformity

[DA-DC-03_PXK](#)

eCAD model

[ETN.PXK-C13_1N_03-A](#)

Installation instructions

[IL019140ZU](#)

Installation videos

[xpole-pxkrebo-installation-video](#)

elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Operating ambient temperature - max

40 °C

Operating ambient temperature - min

-25 °C

Product range

PXK

Rated current

13 A

Rated operational current for specified heat dissipation (I_n)

13 A

Rated switching capacity (IEC/EN 61009)

10 kA

Static heat dissipation, non-current-dependent

0 W

Tripping characteristic

C

Built-in depth

69.5 mm

Current limiting class

3

Rated short-circuit breaking capacity (EN 60947-2)

0 kA

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-25 °C

Fault current rating

0.3 A

Heat dissipation capacity

0 W

Heat dissipation per pole, current-dependent

0 W

Number of poles (protected)

1

Number of poles (total)

2

Rated operational voltage (U_e) - max

240 V

Rated short-circuit breaking capacity (IEC 60947-2)

0 kA

Rated switching capacity

10 kA

Basic function

Combined RCD/MCB devices

Equipment heat dissipation, current-dependent

3.4 W

Rated impulse withstand voltage (Uimp)

4 kV

Degree of protection

IP20

Tripping

Non-delayed

Overvoltage category

III

Pollution degree

2

Impulse withstand current

Partly surge-proof, 250 A

Leakage current type

A

Release characteristic

C

Sensitivity type

Type A, pulse-current sensitive

Frequency rating

50 Hz

Rated insulation voltage (Ui)

440 V

Connectable conductor cross section (solid-core) - min

1 mm²

Connectable conductor cross section (solid-core) - max

25 mm²

Connectable conductor cross section (multi-wired) - min

1 mm²

Connectable conductor cross section (multi-wired) - max

25 mm²

Rated short-circuit breaking capacity (EN 61009)

10 kA

Rated short-circuit breaking capacity (EN 61009-1)

10 kA

Number of poles

Single-pole + N

Disconnection characteristic

Undelayed



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia