

Product datasheet

Specifications



TeSys D thermal overload relays - remote electrical tripping - 110 V DC/AC

Local distributor code:
2210872

LA7D03F

EAN Code: 3389110055122

Main

Range	TeSys
Product or component type	Electrical remote tripping
Device short name	LA7D
Accessory / separate part category	Electrical accessory
Product compatibility	LRD43.. LR3D15.. LR2D LRD33.. LR3D43.. LR3D35.. LRD15.. LR3D33..
[Uc] control circuit voltage	110 V AC 50/60 Hz 110 V DC

Complementary

Maximum inrush power in VA	100 VA
Inrush power in W	0...100 W
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.700 cm
Package 1 Width	4.800 cm
Package 1 Length	5.200 cm
Package 1 Weight	106.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.589 kg

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty (in months)

18



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better



Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Compliant**

REACH Regulation [REACH Declaration](#)

Use Longer



Lifetime extension

Repair **No**

Use Again



Repack and remanufacture

Take-back **No**

WEEE Label  **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**