


FEATURES

- Fix input unregulated single and dual output
- Continuous short-circuit protection.
- Industry standard pin-out
- I/O isolation test voltage 3KVDC
- No-load input current as low as 8mA
- Operating temperature range
 40°C to +105°C
- High efficiency up to 81%
- IEC62368, UL62368, EN62368 approved

RS PRO 1W isolated DC-DC converters

- 2233687, 2233688, 2233689, 2233691,
- 2233696, 2233697, 2233698, 2233699



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

PCB Mount DC-DC converters are specially designed for applications where an isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits. Featuring continuous short circuit protection and no-load input current as low as 8mA

General Specifications

Model	DC-DC 1W Isolated (3KV) DC-DC converter
Mounting Type	PCB
MTBF	MIL-HDBK-217F@25°C > 3,500,000 hrs
Applications	Industrial control systems, instrumentation, analogue, relay-driven and data switching circuits.

Input Vo		(Vdc)	Output	Output		Max.	Efficiency
RS Stock#	Nominal	Max	Voltage	Current	Wattage	Capacitive Load(µF)	(Typ)
2233687				±100/±10mA	1W	1200	80%
2233688			±12V	±42/±5mA	1W	220	81%
2233689			±15V	±34/±4mA	1W	220	81%
2233691	12V	12V (10.8-13.2)		±21/±2mA	1W	100	80%
2233696	(10.8-13.2			200/20mA	1W	2400	80%
2233697			12V	83/9mA	1W	560	80%
2233698			15V	67/7mA	1W	560	81%
2233699			24V	42/5mA	1W	220	81%

Input Specifications

Input Specification					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Input Current (full load / no-load)	12VDC input	-	112/8	118/	mA
Reflected Ripple Current	Nominal input voltage	-	15	-	
Surge Voltage (1sec. max.)	12VDC input	-0.7	-	18	VDC
Input Filter		Capacitance Filter			
Hot Plug		Unavailable			



Output Specifications

Output Specification						
Item	Operating Condit	ions	Min	Тур.	Max	Unit
Voltage Accuracy			See out	See output regulation curves (Fig. 1)		
Lincon Dogulation	Input voltage	3.3VDC output	-	-	±1.5	%
Linear Regulation	change: ±1%	Others	-	-	±1.2	
Load Regulation 10%	10% -100% load	3.3VDC output	-	15	20	
		5VDC output		10	15	
		Others		8	10	
Temperature Coefficient	100% load		-	±0.02	-	%/°C
Ripple & Noise *	20MHz bandwidth	Others	-	30	75	m)/ n n
		24VDC output		50	100	mV p-p
Short circuit Protection			Co	ontinuous,	self-recove	γ


Note: * The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information.


General Specifications


Item	Operating Conditions	Min	Тур	Max.	Unit
Isolation	Input-output electric strength test for 1 minute with a leakage current of 1mA max.	3000	-	-	VDC
Insulation Resistance	Input-output resistance at 500VDC	1000	-	-	МΩ
Isolation Capacitance	Input-output capacitance at 100KHz/0.1V		20		pF
Operating Temperature	See Fig. 1	-40	-	+105	°C
Storage Temperature		-55	-	+125	L L
Case Temperature Rise	Ta=25°C	-	25	-	
Storage Humidity	Non-condensing	5	-	95	%RH
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds	-	-	300	°C
Vibration		10-150Hz, 5G, 0.75mm. along X,Y and Z axis		g X,Y and	
Switching Frequency *	Full load, nominal input voltage	-	260	-	KHz
MTBF	MIL-HDBK-217F@25°C		3500		K hours





Typical Performance Curves













Design Reference

Typical application

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig.3. Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer




Table 1: Recommended input and output capacitor values

Vin	Cin	Single output	Cout	Dual output	Cout
		5VDC	10μF16V	±5VDC	4.7μF/16V
12VDC	2.2μF/25V	12VDC	2.2μF/25V	±12VDC	1μF/25V
IZVDC	2.2με/25ν	15VDC	1μF/25V	±15VDC	0.47μF/25V
		24VDC	1μF/50V	±24VDC	0.47μF/50V



EMC compliance circuit

Dual




Fig 4.

Table 2: EMC recommended circuit value table

	C1	4.7μF /50V
Emissions	C2	4.7μF /50V
	CY	270pF/3000VDC
	C3/C4	Refer to the Cout in table 1
	LDM	6.8µH

EMC Specifications


Funitariana	CE	CISPR32/EN55032 CLASS B	
Emissions	RE	CISPR32/EN55032 CLASS B	
Immunity	ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±6kV	Perf. Criteria B
Note: Refer to Fig	g.4 for recommended cir	cuit test	




Mechanical Specifications

Case material	Black plastic; flame-retardant and heat-resistant (UL94 V-0)
Dimensions	19.65 x 6.00 x 10.16mm
Weight	2.1g (Typ.)
Cooling Method	Free air convection

Dimensions and recommended layout





Note: Grid 2.54*2.54mm

	Pin-Out	
Pin	Single	Dual
1	Vin	Vin
2	GND	GND
5	0V	-Vo
6	No Pin	OV
7	+Vo	+Vo

Approvals

Safety Certification	IEC62368, UL62368, EN62368 approved
----------------------	-------------------------------------



- 1. If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet.
- 2. The maximum capacitive load offered were tested at input voltage range and full load.
- 3. Unless otherwise specified, parameters in this datasheet were measured under the conditions of $Ta=25^{\circ}C$, humidity
- 4. Our products shall be classified according to ISO14001 and related environmental laws and regulations.