

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Product description

The ILC 151 ETH modular small-scale controller for the Inline I/O system is at the heart of Easy Automation. The ILC 1X1 series is characterized by its support for the Modbus/TCP and PROFINET Ethernet-based protocols. A new feature is the support for an optional SD card.

Your advantages

- Memory extendable by up to 2 GB via plug-in SD card
- Free engineering with PC Worx Express (IEC 61131-3)
- Complete INTERBUS master (4096 I/O points)
- PROFINET-Device
- Modbus/TCP-Client
- Integrated FTP and HTML5 web server
- Numerous protocols supported such as: HTTP, FTP, SNTP, SNMP, SMTP, SQL, MySQL, etc.

Commercial data

Item number	2700974
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRA
Product key	DRAAAA
Catalog page	Page 49 (C-6-2019)
GTIN	4046356665506
Weight per piece (including packing)	363 g
Weight per piece (excluding packing)	348.2 g
Customs tariff number	85371091
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Product properties

Product type	Controller
Product family	Inline-Controller
Type	modular

Display

Diagnostics display	no
---------------------	----

System properties

Processor	AlteraNios® II 64 MHz
Retentive data storage	8 kByte (NVRAM)

IEC 61131 runtime system

Program memory	256 kByte
Data storage system	256 kByte
Number of control tasks	8

INTERBUS-Master

Amount of process data	max. 4096 bit (INTERBUS)
Number of supported devices	max. 128
Number of local bus devices that can be connected	max. 63 (observe current consumption)
Number of devices with parameter channel	max. 16
Number of supported branch terminals with remote bus branch	max. 3

Modbus/TCP-Client

Amount of process data	max. 16384 bit (internal Modbus /TCP client)
Number of Modbus/TCP clients	max. 8 later than FW 4.42

PROFINET

Device function	PROFINET device
Specification	2.2
Device ID	007E _{hex} / 126 _{dez}
Vendor ID	00B0 _{hex} / 176 _{dez}

Function

Diagnostics display	no
Redundancy function	no

Safety function	no
-----------------	----

Functionality

Programming languages supported	Instruction list (IL)
	Symbolic flowchart (SFC)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)

System requirements

Engineering tool	PC Worx
	PC Worx Express
Configuration tool	Config+ Version 1.01 or later
Diagnostics tool	DIAG+
Runtime system	eCLR
Application interface	OPC

Electrical properties

Transmission medium	Copper
---------------------	--------

Real-time clock

Realtime clock	yes
Description realtime clock	integrated (rechargeable battery buffered)

Potentials: 24 V supply U_{ILC}

Supply voltage	24 V DC -15 % / +20 % (in accordance with EN 61131-2)
Supply voltage range	19.2 V DC ... 30 V DC
Current draw	80 mA (without connected I/O terminal blocks)

Potentials: 7.5 V communications power U_L (potential jumper)

Supply voltage	7.5 V DC $\pm$ 5 %
----------------	--------------------

Potentials: 24 V analog supply U_{ANA} (potential jumper)

Supply voltage	24 V DC -15 % / +20 %
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

Potentials: 24 V main supply U_M

Supply voltage	24 V DC -15 % / +20 % (in accordance with EN 61131-2)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 8 A DC
	6 mA (without sensors)

Potentials: 24 V segment supply U_S

Supply voltage	24 V DC -15 % / +20 % (in accordance with EN 61131-2)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 8 A DC
	10 mA (without actuators)

Input data

Digital:

Input name	Digital inputs
Description of the input	EN 61131-2 type 1 NPN/PNP
Number of inputs	8
Cable length	max. 30 m
Connection method	Inline potential distributor
Connection technology	2-, 3-, 4-conductor
Input voltage range	-0.5 V ... 30 V
Input voltage range "0" signal	-0.5 V ... 5 V
Input voltage range "1" signal	15 V ... 30 V
Nominal input current at U_{IN}	typ. 7 mA max. 15 mA
Input filter time	typ. 5 ms (Signal change 0→  typ. 5 ms ()

Output data

Digital:

Output name	Digital outputs
Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Number of outputs	4
Maximum output current per channel	500 mA
Maximum output current per module / terminal block	2 A
Nominal load, lamp	12 W
Nominal load, ohmic	12 W

Connection data

Inline connector

Connection method	Spring-cage connection
Conductor cross section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16

Interfaces

Web server	yes
------------	-----

Ethernet

Bus system	RJ45
Number of interfaces	1
Connection method	RJ45 jack
Transmission speed	10/100 Mbps

ILC 151 ETH - Controller



2700974

<https://www.phoenixcontact.com/in/products/2700974>

No. of channels	1
-----------------	---

INTERBUS local bus (master)

Number of interfaces	1
Connection method	Inline data jumper
Transmission speed	500 kBaud / 2 MBaud (can be switched)

Parameterization/operation/diagnostics

Bus system	RS-232
Number of interfaces	1
Connection method	6-pos. MINI DIN socket (PS/2)
Transmission speed	max. 115.2 kbps
Transmission physics	Copper
No. of channels	1

Dimensions

Width	80 mm
Height	119.8 mm
Depth	71.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Shock	25g, Criterion 1, according to IEC 60068-2-27
Vibration (operation)	5g
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Resistance to gases that may endanger the functions, in acc. with DIN 40046-36, DIN 40046-37	Sulfur dioxide (SO ₂) 10 ±0.3 ppm (test duration: 10 days), hydrogen sulfide (H ₂ S) 1 ±0.3 ppm (test duration: 4 days), both at 25°C and with 75% humidity

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	Immunity test in accordance with EN IEC 61000-6-2 Electrostatic discharge (ESD) IEC 61000-4-2 Criterion B, ±6 kV contact discharge, ±8 kV air discharge Immunity test in accordance with EN IEC 61000-6-2 Electromagnetic fields IEC 61000-4-3 Criterion A, Field intensity: 10 V/m

ILC 151 ETH - Controller



2700974

<https://www.phoenixcontact.com/in/products/2700974>

	Immunity test in accordance with EN IEC 61000-6-2 Fast transients (burst)IEC 61000-4-4 Criterion A, all interfaces ± 1 kVCriterion B, all interfaces ± 2 kV
	Immunity test in accordance with EN IEC 61000-6-2 Transient overvoltage (surge)IEC 61000-4-5 Criterion B; DC supply lines: ± 0.5 kV/ ± 1.0 kV (symmetrical/asymmetrical), fieldbus cable shielding: ± 1.0 kV
	Immunity test in accordance with EN IEC 61000-6-2 Conducted interferenceIEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN 61000-6-4/IEC 61000-6-4 Class A

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2700974>



EAC

Approval ID: RU*DE*08.B.00529/19



LR

Approval ID: LR23398855TA

BSH

Approval ID: 858



RINA

Approval ID: ELE121121XG

ABS

Approval ID: 22-2226444-PDA



cULus Listed

Approval ID: E238705

DNV

Approval ID: TAA00002CU



cULus Listed

Approval ID: E199827

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



Classifications

ECLASS

ECLASS-11.0	27242207
ECLASS-12.0	27242207
ECLASS-13.0	27242207

ETIM

ETIM 9.0	EC000236
----------	----------

UNSPSC

UNSPSC 21.0	32151700
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6c30b054-6cee-47f6-9b39-a504876fff1b
EF3.0 Climate Change	
CO2e kg	40.6 kg CO2e

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



Accessories

COM CAB MINI DIN - Connecting cable

2400127

<https://www.phoenixcontact.com/in/products/2400127>

Connecting cable, for connecting the controller to a PC (RS-232) for PC WORX with flow control, 3 m in length



SD FLASH 512MB - Program/configuration memory

2988146

<https://www.phoenixcontact.com/in/products/2988146>

Program and configuration memory, plug-in, 512 Mbyte.



ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



SD FLASH 512MB APPLIC A - Program/configuration memory

2701799

<https://www.phoenixcontact.com/in/products/2701799>



Program and configuration memory for extending the internal Flash memory, plug-in, 512 MB with license key for function block libraries. For licensed function blocks, please refer to the documentation.

SD FLASH 2GB - Program/configuration memory

2988162

<https://www.phoenixcontact.com/in/products/2988162>



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



SD FLASH 2GB APPLIC A - Program/configuration memory

2701190

<https://www.phoenixcontact.com/in/products/2701190>



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB with license key for function block libraries. For licensed function blocks, please refer to the documentation.

AX OPC SERVER - Driver and interface software

2985945

<https://www.phoenixcontact.com/in/products/2985945>



AX OPC SERVER, communication interface for OPC-capable visualization with PC WORX-based controls.

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



IPASSIGN - Software

2701094

<https://www.phoenixcontact.com/in/products/2701094>



IPAssign is an easy to use tool for setting the IP address of devices which rely on BOOTP. No installation or administrative rights are required to use IPAssign.

This product is free and only available from the "Downloads" tab.

RESY+ - Function block

2400295

<https://www.phoenixcontact.com/in/products/2400295>



Resy+ includes function block libraries. The control technology from Phoenix Contact supplements remote control protocols, such as IEC 60870-5-101/104, Modbus TCP/RTU, and ODP (Open Data Port). Resy+ is used in water management, the gas sector, and the energy industry, for example. The function blocks can be downloaded.

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



PC WORX UA SERVER-PLC 10 - Driver and interface software

2402684

<https://www.phoenixcontact.com/in/products/2402684>



OPC UA server for communication with a maximum of 10 modular small-scale controllers (AXC 1xxx or ILC 1x1)

PC WORX UA SERVER-PLC 40 - Driver and interface software

2402685

<https://www.phoenixcontact.com/in/products/2402685>



OPC UA server for communication with a maximum of 25 controllers

ILC 151 ETH - Controller

2700974

<https://www.phoenixcontact.com/in/products/2700974>



PC WORX UA SERVER-PLC 80 - Driver and interface software

2402686

<https://www.phoenixcontact.com/in/products/2402686>

OPC UA server for communication with a maximum of 200 controllers



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in