



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-Code Pigtail, Female, Straight



Cable Assembly Type: **M12 Pigtail**

Number of Positions: **8**

Cable Assembly Length: **5 m**

M8/M12 Application Type: **Sensor/Actuator**

Connector & Keying Code: **A**

[All M12 A-Code Pigtail, Female, Straight \(0\)](#)

Features

Product Type Features

Cable Assembly Type	M12 Pigtail
Cable Assembly (End A)	M12 Socket

Configuration Features

Configuration Number	A
Number of Positions	8

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Body Features

Jacket Material	PUR
Connector Color (End A)	Blue
Cable Color	Gray
Wire Color (Base)	Brown, White, Blue, Black, Gray, Pink, Violet, Orange
Connector & Keying Code	A



Contact Features

Contact Current Rating (Max)	2 A
------------------------------	-----

Mechanical Attachment

Thread Size	M12
Connector Orientation (End A)	Straight

Housing Features

Housing Material	Plastic
------------------	---------

Dimensions

Outside Cable Diameter	6 mm[.236 in]
Wire Size	24 AWG

Operation/Application

M8/M12 Application Type	Sensor/Actuator
Shielded	No

Packaging Features

Packaging Method	Box
Packaging Quantity	25

Other

Field Serviceable	Yes
Cable Assembly Length	5 m
Cable Assembly Configuration	Single Ended

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #CAT-AM78-H342

AMPSEAL PCB Vertical Headers



TE Part #1838274-2

M12 Fld Ser CONN. Female Skt Sldr



TE Part #1-66099-4

III+ PIN,18-16,30AU/FL,SMPACK



TE Part #CAT-L489-CH8172

LEAVYSEAL Connector Housings



TE Part #3-640428-8

08P MTA156 CONN ASSY 22AWG RED



TE Part #350735-4

12P UMNL PLUG HSG UL94VO

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2273041-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2273041-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2273041-3_A.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages
 - M8 / M12 Connector System Catalog
 - English
 - M8 / M12 Connector System Catalog
 - Japanese

- Product Specifications
 - Application Specification
 - English