

Features

- Maximum operating pressure is 30 bar.
- Operating temperature range -20°C to +100°C.
- Material: Steel / Plastic with Nickel- and Zinc plated Finish
- Single Shut Off (One side is with valve)
- DN5.5
- ISO 6150-B-12
- Industrial Interchangeable 1/4"
- 1-Stage
- Compatible with:
Industrial interchange 1/4"
TST 024
PARKER - RECTUS 23
CEJN 310
HANSEN 3000
PARKER 20
ATLAS COPCO QIC 08
US-MIL-SPEC-C-4109

RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0325556



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Series 23.06 Quick Connect Couplings

Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.

1-Stage coupling. Simply pressing the button once starts a fully automatic disconnection process: closure of the upstream compressed air circuit, decompression of the downstream circuit, automatic disconnection of the plug as soon as the pressure is low enough.


- Maximum operating pressure is 30 bar.
- Operating temperature range -20°C to +100°C.
- Material: Steel / Plastic with Nickel- and Zinc plated Finish
- Single Shut Off (One side is with valve)
- DN5.5
- ISO 6150-B-12
- Industrial Interchangeable 1/4"
- 1-Stage
- Compatible with:

Industrial interchange 1/4"	TST 024	PARKER - RECTUS 23
CEJN 310	HANSEN 3000	PARKER 20
ATLAS COPCO QIC 08	US-MIL-SPEC-C-4109	


Specifications

Manufacturer Series	023.06
Coupling Type	Quick Connect Coupling Socket
Connection Standard	DN 5.5 ISO 6150-B-12 & Industrial Interchange 1/4"
Connection Standard Compatible With	Industrial interchange 1/4"; TST 024; PARKER - RECTUS 23; CEJN 310; HANSEN 3000; PARKER 20; ATLAS COPCO QIC 08; US-MIL-SPEC-C-4109
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	30bar
Flow	1-Stage
Flow Direction & Sealing	Self-sealing coupling
Material	Steel, Plastic
Finish	Nickel, Zinc Plated
Connection Type	Threaded
Thread Size	1/4 in
Thread Standard	G
Thread Gender	Male
Coupling Gender	Male
Threaded Connection	G 1/4 Male
Seal material	Nitrile Rubber
Hose Barb Connection	N/A

Specifications



Dimensions (mm)		
SW	L	ØD
22	62.4	27.5





Material Code

A = Steel Zinc Plated

B = Steel

C = Plastic

S = Steel Nickel Plated



Series 23.06 Quick Connect Couplings




0 - 30 bar
(0-435 PSI)



-20° to +100°C (NBR)
-4° to +212°F

Shut Off
Type



OM 200 - 00700
02306GC00M

1 - STAGE

DN

5.5 mm