

angular gearbox straight teeth GBY-Ø 80 mm - reduction 12:1<15 arc.min -120 N.m

GBY080012K

EAN Code: 3606480388750

Main

Range compatibility	Lexium ILS
	Lexium 62 ILM
	Lexium 62
	Lexium 32
	Lexium 32i
	Lexium 52
	Lexium SD3
Gear box type	Straight teeth
Product or component type	Angular planetary gearbox
Device short name	GBY
Product compatibility	BMI (70 mm, 2 motor stacks)
	BMI (70 mm, 3 motor stacks)
	BMH (70 mm, 2 motor stacks)
	BMH (70 mm, 3 motor stacks)
	BSH (70 mm, 2 motor stacks)
	BSH (70 mm, 3 motor stacks)
	BMH (100 mm, 1 motor stacks)
	BSH (100 mm, 1 motor stacks)
	BRS3
	ILS (85 mm, 1 motor stacks)
	ILS (85 mm, 2 motor stacks)
	ILS (85 mm, 3 motor stacks)
	SH3
	MH3
	ILM
Gearbox external diameter	80 mm
Reduction ratio	12:1

Complementary

Maximum torsional backlash	15 arc.min
Torsional rigidity	6.5 N.m/arcmin
Housing colour	Black
Housing material	Black anodized aluminium
Shaft material	C 45
Additional information	Lubricated for life
Service life in hours	30000 h at 100 rpm at 30 °C
Mounting position	Any position
Efficiency	95.0 %
Maximum radial force Fr	650 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 $^{\circ}\text{C}$
Maximum axial force Fa	1200 N at 100 rpm, during 30000 hour at 30°C
moment of inertia	1.273 kg.cm²

Continuous output torque	120 N.m at 100 rpm at 30 °C
Maximum output torque	192 N.m at 100 rpm at 30 °C
Net weight	5 kg
Input diameter	19.0 mm
No load running torque	0.1 N.m
Reduction ratio	12
Compatibility code	GBY
Internal length	161.5 mm

Environment

Noise level	73 dB at 1 m, no-load					
IP degree of protection	Shaft output: IP54					
ambient temperature for operation	-2590 °C					

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	9.2 cm
Package 1 Length	22.0 cm
Package 1 Weight	4.119 kg
Unit Type of Package 2	S03
Number of Units in Package 2	2
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.963 kg

Logistical informations

Country of origin DE

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint								
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1180							
Environmental Disclosure	Product Environmental Profile							

Use Better

Packaging made with recycled cardboard	No				
Packaging without single use plastic	No				
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
SCIP Number	7c9e597c-8ccc-4daf-95fb-5d67fc70d561				
REACh Regulation	REACh Declaration				
PVC free	Yes				


Use Again

○ Repack and remanufacture								
Circularity Profile	No need of specific recycling operations							
Take-back	No							

GBY080012K

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	а3	a4	а5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5	a6
161.5	40	36	4	22.5	6	80	60 h7	20 h7	M6 x 10	70	88.3

Values in in.

á	a2	а3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5	a6
6	5.36	1.57	1.42	0.15	0.88	0.19	3.15	2.36 h7	0.78 h7	M6 x 0.39	2.76	3.48