

Specifications



Eaton 185181

Eaton Moeller® series C22 Emergency stop/emergency switching off pushbutton, Mushroom-shaped, 38 mm, Turn-to-release function, 1 NC, 1 N/O, Cable (black) with non-terminated end, 4 pole, 1 m

General specifications

PRODUCT NAME	Eaton Moeller® series C22 Emergency stop/emergency switching off pushbutton
CATALOG NUMBER	185181
MODEL CODE	C22-PVT-K11-P62
EAN	4015081806669
PRODUCT LENGTH/DEPTH	1097 mm
PRODUCT HEIGHT	38 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	0.077 kg
CERTIFICATIONS	VDE 0660 IEC/EN 60947-5-5 CSA CE UL CSA Class No.: 321103 CSA File No.: 165628 IEC/EN 60947-5-1 UL 508 CSA-C22.2 No. 14-10 CSA-C22.2 No. 94-91 CSA-C22.2 No. 94.2-07 CE marking UL File No.: E340491
CATALOG NOTES	Contacts with safety function, by positive opening to IEC/EN 60947-5-1



Powering Business Worldwide

Features & Functions

BASE COLOR	Yellow
DESIGN	Mushroom-shaped Classical
FEATURES	Tamper-proof (according to ISO 13850, EN 418) Positive opening
ILLUMINATION	Non-illuminated
UNLOCKING METHOD	Turn-release

Climatic environmental conditions

AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	30 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30

General

CABLE LENGTH	1 m
CABLE MATERIAL	PUR
CONNECTION TO SMARTWIRE-DT	No
CONNECTION TYPE	Cable (black) with non- terminated end, 4 pole
DEGREE OF PROTECTION	NEMA 4X, 13 IP67/IP69K
MOUNTING METHOD	Built-in
MOUNTING POSITION	As required
OPENING DIAMETER	22.5 mm
OPERATING FREQUENCY	300 Operations/h
OVERVOLTAGE CATEGORY	III
POLLUTION DEGREE	3
PRODUCT CATEGORY	RMQ compact solution
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	800 V AC
SHOCK RESISTANCE	30 g, Mechanical, Shock duration 11 ms
TIGHTENING TORQUE	2 Nm, Threaded ring
TYPE	Controlled stop pushbutton/emergency- stop button

Electrical rating

RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	3 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 24 V	4 A
SHORT-CIRCUIT PROTECTION RATING	Max. 4 A gG/gL, Fuse, Contacts

Actuator

ACTUATING FORCE	50 N
------------------------	------

ACTUATOR COLOR	Red
-----------------------	-----

ACTUATOR DIAMETER	38 mm
--------------------------	-------

ACTUATOR FUNCTION	Turn-to-release
--------------------------	-----------------

ACTUATOR TRAVEL AND ACTUATION FORCE (DIN EN 60947-5-1)	4.65 mm
---	---------

KNOB TRAVEL	5.7 mm
--------------------	--------

Contacts

CONTROL CIRCUIT RELIABILITY

1 failure per 17,000,000
switching operations
(statistically determined,
at 17 V DC/7 mA: N/O
contact
1 failure per 900,000
switching operations
statistically determined, at
17 V DC/7 mA: N/C
contact)

FORCE FOR POSITIVE OPENING - MIN

20 N

NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)

1

NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)

1

Resources

CATALOGUES	eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf
CONTROL TRAVEL DIAGRAM	eaton-operating-circuit-pushbutton-contact-travel-diagram.eps
DECLARATIONS OF CONFORMITY	eaton-emergency-stop-emergency-switching-off-pushbutton-declaration-of-conformity-eu250546en.pdf eaton-emergency-stop-emergency-switching-off-pushbutton-declaration-of-conformity-uk251029en.pdf
DRAWINGS	eaton-operating-c22-dimensions-002.eps eaton-operating-3d-drawing-007.eps eaton-operating-button-symbol.eps
ECAD MODEL	DA-CE-ETN.C22-PVT-K11-P62
FLYERS	eaton-rmq-titan-selection-aid-brochure-fl047002-en-us.pdf
INSTALLATION INSTRUCTIONS	IL047010ZU.pdf
INSTALLATION VIDEOS	Eaton's RMQ compact solution pilot devices
MCAD MODEL	DA-CD-c22_pvt_open_cable DA-CS-c22_pvt_open_cable
SALES NOTES	eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf eaton-rmq-compact-solution-flyer-fl047001en-en-us.pdf eaton-rmq-c22-compact-pilot-device-flyer-fl047013en-en-us.pdf
WIRING DIAGRAMS	eaton-operating-wiring-diagram-005.eps

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

