

SACC-CI-M8FS-4P SMD T - Contact carrier



1412221

<https://www.phoenixcontact.com/gb/products/1412221>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 4-position, Socket, straight, M8, coding: A, PCB mounting, SMD reflow, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1412221 |
| Packing unit | 60 pc |
| Minimum order quantity | 60 pc |
| Sales key | ABQHCS |
| Product key | ABQHCS |
| GTIN | 4046356988681 |
| Weight per piece (including packing) | 2.793 g |
| Weight per piece (excluding packing) | 2.02 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-CI-M8FS-4P SMD T - Contact carrier



1412221

<https://www.phoenixcontact.com/gb/products/1412221>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|--------------------|--|

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Application | Signal |
| Number of positions | 4 |
| Seal present | no |
| Shielded | no |
| Coding | A |
| Thread type | M8 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
|----------------------|-----|

Electrical properties

| | |
|-----------------------|----------------------------|
| Contact resistance | $\leq 3 \text{ m}\Omega$ |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 48 V AC 60 V DC |
| Nominal current I_N | 4 A |

Connection data

| | |
|-------------------|------------|
| Connection method | SMD reflow |
|-------------------|------------|

Material specifications

| | |
|--|------|
| Flammability rating according to UL 94 | V0 |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA |

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M8 |
| Coding | A |

SACC-CI-M8FS-4P SMD T - Contact carrier



1412221

<https://www.phoenixcontact.com/gb/products/1412221>

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection (when plugged in) | IP67 (correctly plugged in and locked) |
| Degree of protection | IP67 (correctly plugged in and locked) IP67, when plugged in |
| Ambient temperature (operation) | -55 °C ... 105 °C (Plug / socket) -55 °C ... 105 °C (without mechanical actuation) |

Standards and regulations

| | |
|--------------------------|------------------------------|
| Standard designation | M8 circular connector |
| Standards/specifications | according to IEC 61076-2-104 |

Mounting

| | |
|---------------|--------------|
| Mounting type | PCB mounting |
|---------------|--------------|

Packaging specifications

| | |
|-------------------|------|
| Type of packaging | Tray |
|-------------------|------|

SACC-CI-M8FS-4P SMD T - Contact carrier


1412221

<https://www.phoenixcontact.com/gb/products/1412221>



Drawings

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

SACC-CI-M8FS-4P SMD T - Contact carrier




1412221

<https://www.phoenixcontact.com/gb/products/1412221>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1412221>

|  cULus Recognized Approval ID: E221474-20160506 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 60 V | 4 A | - | - |

SACC-CI-M8FS-4P SMD T - Contact carrier



1412221

<https://www.phoenixcontact.com/gb/products/1412221>

Classifications

ECLASS

ECLASS-13.0

27440110

ETIM

ETIM 9.0

EC003557

UNSPSC

UNSPSC 21.0

39121400

SACC-CI-M8FS-4P SMD T - Contact carrier



1412221

<https://www.phoenixcontact.com/gb/products/1412221>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 7ae98ddf-726b-4e0e-aeb2-f13cabbb0c8d |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk