



RAST

TE Internal #: 4-1534798-7


Wire-to-Board, 7 Position, 2.5 mm [.098 in] Centerline, Insulation

Displacement (IDC), 1 Row, Natural, PA 6 GF, Standard Edge

Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**

Number of Positions: **7**

Centerline (Pitch): **2.5 mm [.098 in]**

Termination Method to Wire & Cable: **Insulation Displacement (IDC)**

Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	7
Number of Rows	1
Connector Contact Load Condition	Selectively Loaded

PCB Mount Orientation: Right Angle

Electrical Characteristics

Operating Voltage	50 VAC, 250 VAC
-------------------	-----------------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Base Material	Copper Tin
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Mating Retention	Without
Mating Alignment Type	Keyed
Mating Alignment	With
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	PA 6 GF

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
Compatible Insulation Diameter Range	1.2 – 1.6 mm[.047 – .063 in]
Connector Height	7.3 mm[.287 in]
Wire Size	24 – 22 AWG

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

--	--



Glow Wire Rating	GWEPT 750°C (Without Flame)
------------------	-----------------------------

Packaging Features

Packaging Method	Tray
Packaging Quantity	1848

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1534798-6
AMP DUOPLUG MARK II




TE Part # 3-1534798-7
AMP DUOPLUG MK2 CONNECTOR
7P SELECTIVE



TE Part # 8-1534798-8
DUOPLUG MK II CONNECTOR3-20P
SELEK LOAD



TE Part # 3-1534798-5
AMP DUOPLUG MK2 CONNECTOR
5P SELECTIVE



TE Part # 9-1534798-6
AMP DUOPLUG MARK II



TE Part # 3-1534798-6
AMP DUOPLUG MARK II



TE Part # 3-1534798-3
AMP DUOPLUG MK2 CONNECTOR
3P SELECTIVE



TE Part # 4-1534798-0
AMP DUOPLUG MK II CON. 3-20 POS.
SELECTIV



TE Part # 3-1534796-7
AMP DUOPLUG MK2 CONNECTOR 7P




TE Part # 3-1534798-9
AMP DUOPLUG MARK II
CONNECTOR3-20P SELEC

Customers Also Bought



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
WedgeLocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT

Documents

Product Drawings

AMP DUOPLUG MK2 CONNECTOR 7P SELECTIVE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1534798-7_A_c-4-1534798-7-a.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_4-1534798-7_A_c-4-1534798-7-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1534798-7_A_c-4-1534798-7-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[VDE Certificate](#)

English

[VDE Certificate](#)

English

[VDE Certificate](#)

English