

Product data sheet

Specifications



Repacked, relay, Acti9 iRTA, 1 OC, 24VAC to 240VAC, 24VDC, delays energizing of a load

A9E16065W



This repacked option saves 0.702 over the standard condition

Main

Relay application	Time delay relay
Time delay type	Delays energizing of a load
Range	Acti9
Product name	IRT
Device short name	iRTA
Signal contacts composition	1 C/O

Complementary

[Ie] rated operational current	8 A at 250 V AC 8 A at 250 V DC 0.01 A at 5 V DC
Impulse duration	> 100 ms
Local signalling	LED, flashing for time delay LED green for power ON
Type of setting	Rotary knob: time delay configuration
Time delay range	0.1...360000 s
Accuracy error	+/- 10 %
Repeat accuracy	+/- 0.5 %
[Uc] control circuit voltage	24...240 V AC 50/60 Hz 24 V DC
[Us] rated supply voltage	24...240 V AC at 50/60 Hz 24 V DC
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	93 mm
Width	18 mm
Depth	72 mm
Product weight	0.065 kg
Colour	White
Mechanical durability	5000000 cycles
Electrical durability	AC-1: 100000 cycles
Undervoltage behaviour	100 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - terminals	Tunnel type terminals for 2 cable(s) 1.5 mm² flexible with cable end Tunnel type terminals for 2 cable(s) 1.5 mm² flexible without cable end Tunnel type terminals for 2 cable(s) 2.5 mm² rigid with cable end Tunnel type terminals for 2 cable(s) 2.5 mm² rigid without cable end
-------------------------	--

Environment

IP degree of protection	IP20
Immunity to microbreaks	20 ms
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	7.4 cm
Package 1 Length	10.3 cm
Package 1 Weight	80 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.7 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins