





- **Cost effective standard model**
- **Robust and compact design**
- **Fast response time**
- **Wide environmental temperature range**

The ETP-AM-SP-100-10K3435A1 and ETP-AM-SP-M12x1.5-100-10k3435A1 temperature probe provides a cost-effective measurement solution where heat, dust and moisture are prevalent and where a compact and robust high-reliability design is required. The sensor is particularly suitable for demanding temperature monitoring applications on vehicles but with its fast response time and wide environmental temperature range, it is equally well-equipped for measurement of liquids and gases used in medical equipment, test machinery, industrial instrumentation and process control systems.

Specifications	
Element	NTC GAG10K3435A1
Accuracy	± 0.3 K @ +25 °C
Tolerance	± 1% @ 25 °C
Beta value 25/85	3435
Beta tolerance	± 2%
Working temperature	-40°...+180 °C, short term 230 °C
Environmental temperature	-40°...+150°C
Sealing	IP67
Response time in still water t90	7s
Material	
Housing	316 stainless steel
Cable	FEP 4 core AWG24, tinned copper shield, 3.2 mm OD
Heat shrink	Elastomer

Dimensions and Wiring ETP-AM-SP-100-GAG10K3435A1


Order Code: 93638-ETP-AM-SP-100-10K3435A1 (on stock)

Dimensions and Wiring ETP-AM-SP-M12x1.5-100-10k3435A1


Order Code: 94885-ETP-AM-SP-M12x1.5-100-10k3435A1 (on request)

TEMPERATURE PROBE

ETP - AM - SP - 100 - GAG10K3435A1

ETP-AM-SP-M12X1.5-100-10K3435A1



Resistance versus temperature table for 10K3435A1

Temp. °C	KΩ	Temp. °C	KΩ	Temp. °C	KΩ	Temp. °C	KΩ
-40	186	2	25.11	44	5.061	86	1.39
-39	176.4	3	24.07	45	4.891	87	1.352
-38	167.4	4	23.07	46	4.729	88	1.315
-37	158.8	5	22.13	47	4.572	89	1.28
-36	150.7	6	21.22	48	4.421	90	1.245
-35	143.1	7	20.36	49	4.276	91	1.212
-34	135.9	8	19.53	50	4.137	92	1.18
-33	129.1	9	18.75	51	4.003	93	1.149
-32	122.7	10	18	52	3.873	94	1.118
-31	116.6	11	17.28	53	3.749	95	1.089
-30	110.8	12	16.6	54	3.629	96	1.06
-29	105.4	13	15.94	55	3.513	97	1.033
-28	100.2	14	15.32	56	3.402	98	1.006
-27	95.37	15	14.72	57	3.295	99	0.9801
-26	90.76	16	14.15	58	3.192	100	0.9549
-25	86.39	17	13.6	59	3.092	101	0.9305
-24	82.26	18	13.08	60	2.996	102	0.9069
-23	78.35	19	12.58	61	2.903	103	0.8839
-22	74.64	20	12.1	62	2.814	104	0.8616
-21	71.12	21	11.64	63	2.728	105	0.84
-20	67.79	22	11.21	64	2.645	106	0.819
-19	64.63	23	10.79	65	2.565	107	0.7987
-18	61.64	24	10.38	66	2.487	108	0.7789
-17	58.79	25	10	67	2.413	109	0.7597
-16	56.1	26	9.631	68	2.341	110	0.7411
-15	53.53	27	9.278	69	2.271	111	0.723
-14	51.1	28	8.94	70	2.204	112	0.7054
-13	48.8	29	8.615	71	2.139	113	0.6883
-12	46.6	30	8.304	72	2.076	114	0.6718
-11	44.52	31	8.006	73	2.016	115	0.6556
-10	42.54	32	7.72	74	1.957	116	0.64
-9	40.66	33	7.445	75	1.901	117	0.6248
-8	38.87	34	7.182	76	1.846	118	0.61
-7	37.17	35	6.929	77	1.794	119	0.5956
-6	35.55	36	6.687	78	1.743	120	0.5817
-5	34.01	37	6.454	79	1.693	121	0.5681
-4	32.55	38	6.23	80	1.645	122	0.5549
-3	31.15	39	6.015	81	1.599	123	0.542
-2	29.82	40	5.809	82	1.555	124	0.5295
-1	28.56	41	5.611	83	1.511	125	0.5174
0	27.35	42	5.42	84	1.47	126	0.5056
1	26.2	43	5.237	85	1.429	127	0.4941

TEMPERATURE PROBE
ETP - AM - SP - 100 - GAG10K3435A1
ETP-AM-SP-M12X1.5-100-10K3435A1



Resistance versus temperature table for 10K3435A1

Temp. °C	KΩ
128	0.4829
129	0.472
130	0.4614
131	0.4511
132	0.4411
133	0.4313
134	0.4218
135	0.4125
136	0.4035
137	0.3947
138	0.3862
139	0.3778
140	0.3697
141	0.3618
142	0.3541
143	0.3466
144	0.3392
145	0.3321
146	0.3252
147	0.3184
148	0.3118
149	0.3053
150	0.299
151	0.2929
152	0.2869
153	0.2811
154	0.2754
155	0.2698
156	0.2644
157	0.2591
158	0.2539

Temp. °C	KΩ
159	0.2489
160	0.244
161	0.2392
162	0.2345
163	0.2299
164	0.2255
165	0.2211
166	0.2168
167	0.2127
168	0.2086
169	0.2046
170	0.2007
171	0.197
172	0.1932
173	0.1896
174	0.1861
175	0.1826
176	0.1793
177	0.1759
178	0.1727
179	0.1696
180	0.1665
181	0.1634
182	0.1605
183	0.1576
184	0.1548
185	0.152
186	0.1493
187	0.1467
188	0.1441
189	0.1415

Temp. °C	KΩ
190	0.1391
191	0.1366
192	0.1343
193	0.1319
194	0.1297
195	0.1274
196	0.1253
197	0.1231
198	0.121
199	0.119
200	0.117
201	0.115
202	0.1131
203	0.1112
204	0.1094
205	0.1076
206	0.1058
207	0.1041
208	0.1024
209	0.1007
210	0.0991
211	0.0975
212	0.0959
213	0.0944
214	0.0929
215	0.0914
216	0.0899
217	0.0885
218	0.0871
219	0.0858
220	0.0844

Temp. °C	KΩ
221	0.0831
222	0.0818
223	0.0806
224	0.0793
225	0.0781
226	0.0769
227	0.0757
228	0.0746
229	0.0735
230	0.0724
231	0.0713
232	0.0702
233	0.0692
234	0.0681
235	0.0671
236	0.0661
237	0.0652
238	0.0642
239	0.0633
240	0.0624
241	0.0615
242	0.0606
243	0.0597
244	0.0589
245	0.058
246	0.0572
247	0.0564
248	0.0556
249	0.0548
250	0.054