



Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Gold (Au)**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **600 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Orientation	Straight
Mating Pin Diameter	1 mm[.039 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Material Finish	Matte
Wire Contact Termination Area Plating Thickness	2.54 – 6.35 µm[100 – 250 µin]
Contact Type	Pin
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	With



Contact Base Material	Brass
Contact Current Rating (Max)	11.2 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Compatible Insulation Diameter Range	2 – 3.2 mm[.079 – .126 in]
Wire Size	.5 – 1.4 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	4500
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1-172233-6 2 POS MINI UNIV FREE HANG BLUE	 TE Part # 5-2151372-2 OCEAN-2.0-APPLICATOR-S-070F130O-RSA	 TE Part # 172340-1 MINI UMNL PLUG HOUSING 9P	 TE Part # 58707-2 PROCrimp MINI-U-MNL2 DIE
 TE Part # 172336-1 2P MINI UMNL PLUG HOUSING	 TE Part # 172233-1 2 POS MINI UMNL CAP HOUSING	 TE Part # 770580-1 10P MINI UMNL PLUG HSG	 TE Part # 770583-1 16P MINI UMNL PLUG HSG
 TE Part # 1-172157-2 2CIR MINI U-M-N-L CAP RED	 TE Part # 1-172168-2 MINI UNIVERSAL M-N-L PLUG 6P	 TE Part # 172329-1 MINI UNIVERSAL MATE-N-LOK CAP HOUSING 3P	 TE Part # 172161-1 9 CIR UNIV M-N-L CAP



TE Part # 172335-1
MINI UMNL PLUG HOUSING 1P



TE Part # 172341-1
MINI UMNL PLUG HOUSING 12P




TE Part # 172170-1
12 CIR UNIV M-N-L PLUG




TE Part # 172159-1
4 CIR UNIV M-N-L CAP




TE Part # 172337-1
MINI UMNL PLUG HOUSING 3P



TE Part # 770582-1
14P MINI UMNL PLUG HSG



TE Part # 770587-1
24P MINI UMNL PLUG HSG



TE Part # 1-172163-2
15 POS TR MINI UNIV

Also in the Series | Mini-Universal MATE-N-LOK



Connector Caps & Covers(2)



Connector Contacts(89)



Connector Hardware(4)




Power Contacts(89)



Rectangular Connector Housings(104)



Rectangular Power Connectors(196)




Standard Rectangular Connectors(104)

Customers Also Bought



TE Part #172343-1
MINI UNIVERSAL M-N-L HOUSING



TE Part #61795-3
RING 18-14 AWG TPBR




TE Part #3543573002
FLHTC0311-22-0




TE Part #925370-8
MOD IV REC HSG, 2X8P






TE Part #350628-1
[.062 COMM P&S SOK 18-24 PTPBR](#)



TE Part #794103-1
[.062 COMM P&S LANCELESS SCKT](#)



TE Part #61793-1
[RING 18-14 AWG TPST](#)



TE Part #925370-4
[MOD IV REC HSG 2X4 POS](#)



TE Part #172336-1
[2P MINI UMNL PLUG HOUSING](#)



TE Part #207397-1
[HSG,RECEPT 10 POSN,METRIMATE](#)

Documents

Product Drawings

[MINI UMNL SOK 20-16 AWG AU LF](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_1-794406-0_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-794406-0_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-794406-0_B.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-794406-0_D.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-794406-0_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-794406-0_D.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG
English

Product Specifications
Product Specification
English
Product Specification
English