

Rotary Hammer LXT®

DHR171

18V • SDS-PLUS • 17 mm • 1.2 J

Compact, brushless tool for impact and unstressed drilling

A light, short-framed rotary hammer for SDS-PLUS bits with an anti-vibration handle. Suitable for impact and unstressed drilling. Speed can be adjusted between 0 and 680 min⁻¹. Impact energy of 1.2 J and max. drilling capacity of 17 mm in concrete.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Impact Energy	1,2 J
Optimum Drilling Diameter Range in Concrete	3,2 - 10 mm
Max. Drilling Diameter in Concrete	17 mm
Max. Drilling Diameter in Wood	13 mm
Max. Drilling Diameter in Steel	10 mm
Impacts per Minute (IPM)	0 - 4800 min ⁻¹
No load speed	0 - 680 min ⁻¹
Adapted for SDS-PLUS bits	✓
Tool weight with battery	2,1 - 2,8 kg
Electronic brake	✓
Vibration Level, Hammer Drilling Into	11,2 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Compact and lightweight for reduced operator fatigue
- Low power consumption thanks to brushless motor
- 2-mode operation for "Rotation Only" or "Hammering with Rotation"
- Vibration absorbing handle provides comfortable operation
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

198993-4

Grease vessel for bit 100 ml



415486-9

DEPTH GAUGE



821551-8

Makpac case (3)



839387-1

MakPac Type 3 Inner Tray



B-57532

Drill Bit Set SDS-PLUS, 5 pcs



E-07026

Drill and Screw bit set 18 pcs



Other

User manual

Parts drawing