



Semiconductor heater unit CSL 028 400 W, 230 V AC clip attachment

Model	
product brand name	SIVACON
product designation	heater unit
design of the product	Semiconductor
General technical data	
consumed active power rated value	400 W
operating temperature	
• minimum	-45 °C
• maximum	70 °C
volume flow rate free-blowing	45 m³/h
Voltage	
type of voltage of the operating voltage	AC
continuous heating power at 20 °C	400 W
inrush current typical	15 A
operating voltage	
• at AC at 50 Hz rated value minimum	230 V
• at AC at 50 Hz rated value maximum	230 V
• at AC at 60 Hz rated value minimum	230 V
• at AC at 60 Hz rated value maximum	230 V
Protection class	
protection class IP	IP20
Main circuit	
operational current of the slow-blow fuse link	10 A
Product details	
product component	
• blower	Yes
• thermostat	No
Connections	
tightening torque with screw-type terminals maximum	0.8 N·m
type of connection technology	2-pole terminal max. 2.5 mm²
Mechanical Design	
height	111 mm
width	85 mm
depth	90 mm
fastening method	Clip for 35 mm DIN rail
mounting position	air flow direction vertical (air outlet on top)
net weight	0.5 kg
material of the enclosure	plastic
Environmental conditions	
ambient temperature during storage	

- minimum
- maximum

-45 °C  
70 °C

### Approvals Certificates

General Product Approval

other

Environment



[Confirmation](#)

[Environmental Con-  
firmations](#)

### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR2150-4A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR2150-4A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR2150-4A](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR2150-4A)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/24/2025

