

Product datasheet

Specifications



Remote Display, Modicon M171/ M172/M173, flush mounted optimized display

TM173DLED

Main

Range of product	Modicon M171/M172/M173
Product or component type	Display module
Display colour	Monochrome
Supply	External source

Complementary

Display type	2 x 7-segment LED
Number of key	4
Colour	White
[Us] rated supply voltage	24 V AC/DC
Marking	CE UL
Overvoltage category	II
Height	80.5 mm
Width	34.5 mm
Depth	34.6 mm
Product weight	0.041 kg

Environment

Standards	UL 94 EN 60730-1 EN 60730-2-9
Product certifications	UKCA UL CSA
Ambient air temperature for operation	-20...65 °C
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP65
Pollution degree	2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	9.300 cm
Package 1 Length	13.200 cm
Package 1 Weight	113.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	5
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	754.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	49 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	9 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	40 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.3 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
SCIP Number	Ae86ba94-4547-4a45-9448-245a31615fc7
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
Updatability	Yes

Use Again




Repack and remanufacture

Recyclability potential, in %	0
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


Dimensions Drawings

Dimensions



Mounting and Clearance

Mounting



- (1) Insert the device
- (2) Secure it with the special brackets provided
- (3) Front panel only (tested in accordance with EN 60529 with a steel sheet 2 mm (0.08 in.) thick $\pm 10\%$)

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative



