




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Right Angle**

Connector System: **Board-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Partially Shrouded
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Connector Contact Load Condition	Fully Loaded
Board-to-Board Configuration	Perpendicular
PCB Mount Orientation	Right Angle
Number of Positions	2
Number of Rows	1

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	750 VACrms
---------------------------------------	------------

Body Features



Connector Profile	Standard
Primary Product Color	Green

Contact Features

Contact Mating Area Plating Material Thickness	.38 μm[15 μin]
Mating Tab Width	1.6 mm[.063 in]
Contact Mating Area Length	10 mm[.393 in]
Contact Base Material	Brass
Mating Tab Thickness	.79 mm[.031 in]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	3 A

Termination Features

Rectangular Termination Post & Tail Width	.9 mm[.035 in]
Rectangular Termination Post & Tail Thickness	.8 mm[.031 in]
Termination Post & Tail Length	3.3 mm
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Alignment Type	Polarization
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polycarbonate GF
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

PCB Thickness (Recommended)	1.6 mm[.06 in]
-----------------------------	----------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0



Packaging Features

Packaging Quantity	1000
Packaging Method	Carton

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 181299-2
MOD 1 CONTACT REC



TE Part # 280590
AMPMODU MOD 1 REC HOUSING



TE Part # 181299-1
MOD 1 CRIMP CONTACT



TE Part # 182198-1
MOD 1 CONTACT



Also in the Series

AMPMODU MOD 1

Board-to-Board Headers & Receptacles(105)	Board-to-Board Jumpers & Shunts(5)	Connector Contacts(75)	Connector Hardware(2)
Power Contacts(1)	Rectangular Power Connectors(20)	Wire-to-Board Connector Assemblies & Housings(16)	

Customers Also Bought

 TE Part #280378-1 4P AMPMODU II SHRD HDR, RT ANG, TIN	 TE Part #280609-2 2P MOD 1 SHROUDED HEADER, ST, 0.4 Au	 TE Part #61372-1 110 FASTON FLAG REC 22-18 AWG TPBR	 TE Part #926498-1 KEYING PART
 TE Part #826469-6 2X6P MOD II SHROUDED HEADER, ST	 TE Part #1-1761682-1 IDC LOW PRO HDR 34P RA HT BLACK	 TE Part #284798-1 CRIMPED TAB CONTACT, P.C.B. INTERFACE	 TE Part #826468-4 4P MOD II SHROUDED HEADER, RT ANG.
 TE Part #826467-6 6P MOD II SHROUDED HEADER, ST	 TE Part #826469-8 2X8P MOD II SHROUDED HEADER, ST		



Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_280615-2_S.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_280615-2_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280615-2_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English