



中国认可
检测
TESTING
CNAS L0748



230014349552



NO.1124020374

检测报告

Test Report

样品名称：可充电锂离子电池组 18650-3.7V-2200mAh-1S1P 3.7V
2200mAh 8.14Wh

Name of Sample: Rechargeable Li-ion Battery 18650-3.7V-2200mAh-1S1P
3.7V 2200mAh 8.14Wh

委托单位：深圳量纬科技有限公司

Consignor: Shenzhen Liangwei Technology Co., LTD



上海化工院检测有限公司

Shanghai Institute of Chemical Industry Testing Co., Ltd.

声 明

Statement

1. 检测报告无本实验室公章（或检验检测专用章）无效。

The test report is invalid if it is not affixed the official seal of the laboratory to it.

2. 复制检测报告未重新加盖本实验室公章（或检验检测专用章）无效。

Copies of the test report without the official seal of the laboratory are invalid.

3. 检测报告无编制、审核、批准人签字无效。

The test report is invalid without the signatures of compiler, checker and approver.

4. 检测报告涂改无效。

The test report is invalid if it is blotted out.

5. 未经本实验室书面批准，不得部分复制检测报告。

It is forbidden to copy the test report partially without the written approval of the laboratory.

6. 送样委托检测结果，仅对所送样品有效。

The conclusion of the consignment test is only valid for the provided sample.

7. 本检测报告以中文为准，英文文本（如有）仅为译文，两者发生冲突时，应以中文文本为准。

The test report has been drafted in Chinese and translated into English (if exist) for convenience only. In the event of discrepancy, the Chinese version shall prevail.

8. 除另有说明，检测检验类别都是指委托分析。

Unless noted otherwise, the test type is consignment test.

地址：上海市云岭东路 345 号

Address: No.345 East Yunling Road, Shanghai

邮政编码(Post Code): 200062

电话(Tel): (021) 31765555

传真(Fax): (021) 31015117

网址 (web site): www.ghs.cn

电子信箱 (E-mail): center@ghs.cn

上海化工院检测有限公司
检测报告

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1124020374

1/11

样品名称 Name of Sample	中文 Chinese	可充电锂离子电池组 18650-3.7V-2200mAh-1S1P 3.7V 2200mAh 8.14Wh	
	英文 English	Rechargeable Li-ion Battery 18650-3.7V-2200mAh-1S1P 3.7V 2200mAh 8.14Wh	
样品编号 Sample No.	1124020374		
委托单位 Consignor	深圳量纬科技有限公司 Shenzhen Liangwei Technology Co., LTD		
生产单位 Manufacturer	深圳量纬科技有限公司 Shenzhen Liangwei Technology Co., LTD		
检测方法 Test method	联合国《试验和标准手册》 ST/SG/AC.10/11/Rev.7&Amend.1 38.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3		
判定标准 Criterion	联合国《试验和标准手册》 ST/SG/AC.10/11/Rev.7&Amend.1 38.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3		
样品外观 Appearance	蓝色 圆柱型塑料薄膜外壳 Blue Cylinder plastics film shell		
样品接受日期 Accepted Date	2024-02-28	检测起迄日期 Test Date	2024-03-11 ~ 2024-04-08
检测项目 Test Items	高度模拟;热测试;振动;冲击;外短路;撞击;过充电;强制放电 Altitude simulation,Thermal test,Vibration,Shock,External short circuit,Impact,Overcharge,Forced discharge		
检测结论 Conclusion	经检测,该样品符合联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3标准要求。 The sample has passed the test items of UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 生效日期(Date): 2024-04-08		
备注 Comment	可充电单电芯电池Rechargeable Single Cell Battery./		
委托单位地址 Consignor Address	/		邮政编码 Post Code 518116

批准
Approver:
职务
Title:

许锐

审核
Checker:

陈建峰

编制
Compiler:

傅佳

电化学测试部部长(Head of Electrochemical Testing Department)



上海化工院检测有限公司 检测报告

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1124020374

2/11

序号 No.	检测项目名称 Name of Test Items	标准要求或标准条款号 Standard requirement or The Clause Number of Standard	检测结果 Test Result	本项结论 Conclusion	备注 Remark
1	高度模拟 Altitude simulation	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.1 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.1	见附表 1 See Appendix 1	合格 Passed	/
2	热测试 Thermal test	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.2 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.2	见附表 2 See Appendix 2	合格 Passed	/
3	振动 Vibration	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.3	见附表 3 See Appendix 3	合格 Passed	/
4	冲击 Shock	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.4 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.4	见附表 4 See Appendix 4	合格 Passed	/
5	外短路 External short circuit	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.5 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.5	见附表 5 See Appendix 5	合格 Passed	/
6	撞击 Impact	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.6 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.6	见附表 6 See Appendix 6	合格 Passed	/
7	过充电 Overcharge	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.7 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.7	见附表 7 See Appendix 7	合格 Passed	/
8	强制放电 Forced discharge	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7&Amend.1 38.3 试验T.8 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7&Amend.1 Section 38.3 Test T.8	见附表 8 See Appendix 8	合格 Passed	/
检测环境条件 Test Environment Condition		环境温度:21℃-22℃;环境湿度:/% Ambient temperature:21℃-22℃;Ambient humidity:/%			
分包检验情况 Subcontracted Test Condition		检测项目 Test Item	/		
		分包实验室 Subcontracted Laboratory	名称 Name	邮编 Post Code	/
			地址 Address	电话 Tel	/

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 1

3/11

[illegible]

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 3

5/11

序号 No.	3	检测项目名称 Name of Test Items		振动 Vibration				
样品 编号 Sample No.	样品状态 Sample Status	试验前 Before		试验后 After		质量损失 Mass Loss /%	剩余电压 Residual OCV /%	其他 现象 Other Event
		质量 Mass /g	开路电压 OCV /V	质量 Mass /g	开路电压 OCV /V			
001	ICYC完全充电 ICYC Fully charged	47.5854	4.05	47.5811	4.04	0.01	99.75	O
002	ICYC完全充电 ICYC Fully charged	47.7202	4.06	47.7162	4.06	0.01	100.00	O
003	ICYC完全充电 ICYC Fully charged	47.4915	4.07	47.4875	4.06	0.01	99.75	O
004	ICYC完全充电 ICYC Fully charged	47.5251	4.06	47.5242	4.05	0.00	99.75	O
005	ICYC完全充电 ICYC Fully charged	47.6867	4.08	47.6859	4.07	0.00	99.75	O
006	25CYC完全充电 25CYC Fully charged	47.7207	4.07	47.7166	4.07	0.01	100.00	O
007	25CYC完全充电 25CYC Fully charged	47.4998	4.08	47.4971	4.07	0.01	99.75	O
008	25CYC完全充电 25CYC Fully charged	47.8896	4.07	47.8878	4.07	0.00	100.00	O
009	25CYC完全充电 25CYC Fully charged	47.8441	4.07	47.8398	4.06	0.01	99.75	O
010	25CYC完全充电 25CYC Fully charged	47.7646	4.06	47.7604	4.05	0.01	99.75	O
以下空白	This space intentionally left blank							

检测报告-附表4

NO. 1124020374

6/11

[illegible]

序号 No.	5	检测项目名称 Name of Test Items	外短路 External short circuit
样品编号 Sample No.	样品状态 Sample Status	样品表面最高温度 Max. External Temperature /℃	其他现象 Other Event
001	1CYC完全充电 1CYC Fully charged	56.4	O
002	1CYC完全充电 1CYC Fully charged	56.8	O
003	1CYC完全充电 1CYC Fully charged	57.2	O
004	1CYC完全充电 1CYC Fully charged	57.2	O
005	1CYC完全充电 1CYC Fully charged	56.1	O
006	25CYC完全充电 25CYC Fully charged	57.7	O
007	25CYC完全充电 25CYC Fully charged	57.7	O
008	25CYC完全充电 25CYC Fully charged	57.8	O
009	25CYC完全充电 25CYC Fully charged	57.5	O
010	25CYC完全充电 25CYC Fully charged	56.5	O
以下空白	This space intentionally left blank		

备注：D-解体 R-破裂 F-起火 O-无解体、无起火、无破裂。

Note: D-Disassembly R-Ruptur F-Fire O-No Disassembly,No Fire & No Rupture.

[illegible]

检测报告-附表7

NO. 1124020374

9/11


[illegible]

上海化工院检测有限公司
检测报告-附表8
Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 8

NO. 1124020374

10/11

序号 No.	8	检测项目名称 Name of Test Items	强制放电 Forced discharge
样品编号 Sample No.	样品状态 Sample Status	其他现象 Other Event	
029	1CYC完全放电 1CYC Fully discharged	O	
030	1CYC完全放电 1CYC Fully discharged	O	
031	1CYC完全放电 1CYC Fully discharged	O	
032	1CYC完全放电 1CYC Fully discharged	O	
033	1CYC完全放电 1CYC Fully discharged	O	
034	1CYC完全放电 1CYC Fully discharged	O	
035	1CYC完全放电 1CYC Fully discharged	O	
036	1CYC完全放电 1CYC Fully discharged	O	
037	1CYC完全放电 1CYC Fully discharged	O	
038	1CYC完全放电 1CYC Fully discharged	O	
039	25CYC完全放电 25CYC Fully discharged	O	
040	25CYC完全放电 25CYC Fully discharged	O	
041	25CYC完全放电 25CYC Fully discharged	O	
042	25CYC完全放电 25CYC Fully discharged	O	
043	25CYC完全放电 25CYC Fully discharged	O	
044	25CYC完全放电 25CYC Fully discharged	O	
045	25CYC完全放电 25CYC Fully discharged	O	
046	25CYC完全放电 25CYC Fully discharged	O	
047	25CYC完全放电 25CYC Fully discharged	O	
048	25CYC完全放电 25CYC Fully discharged	O	
备注: D-解体 F-起火 O-无解体、无起火。 Note: D-Disassembly F-Fire O-No Disassembly & No Fire.			



DL 18650-2200mAh 2200mAh 3.7V
23L04V0 123L26 00 1499

Rechargeable Li-ion Battery
Model: 18650-3.7V-2200mAh-1S1P
Rated Voltage: 3.7V
Rated Capacity: 2200mAh / 8.14Wh
Date in produced: 2024.01
Manufacturer: Shenzhen Liangwei

Manufacturer: Shenzhen Liangwei
Technology Co., Ltd



报告结束