



Example image

APPLICATION PURPOSES

- For cold and hot potable water
- For technical building systems, industry and shipbuilding
- Exclusively for absorption of axial linear expansion during operation
- Suitable exclusively for liquid media

CHARACTERISTICS

- Pressing indicator
- Silicone-free (LABS-free)
- Leaky if unpressed
- Bellows made of stainless steel
- Seal ring made of CIIR, black

- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating pressure	≤ 16 bar
Operating temperature	-30 – +120 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	D cm	La (+/-) mm	L cm	Z cm
These articles are suitable for the following system: Geberit Mapress Stainless Steel (silicone-free)						
33932	12	15	2.6	7	15.1	11.1
33933	15	18	2.6	7	14.7	10.7
33934	20	22	3.1	11	10.6	6.4
33935	25	28	3.9	13	12	7.4

Art. no.	DN	d _ø mm	D cm	La (+/-) mm	L cm	z cm
33936	32	35	4.6	13	13.9	8.7
33937	40	42	5.9	13	14.9	8.9
33938	50	54	7	18	17.6	10.6
33939	65	76.1	8.8	22	26.2	15.6
33940	80	88.9	11.7	23	28.6	16.6
33941	100	108	13.7	23	54.2	39.2

These articles are suitable for the following system: **Geberit Mapress Stainless Steel**

33932	12	15	2.6	7	15.1	11.1
33933	15	18	2.6	7	14.7	10.7
33934	20	22	3.1	11	10.6	6.4
33935	25	28	3.9	13	12	7.4
33936	32	35	4.6	13	13.9	8.7
33937	40	42	5.9	13	14.9	8.9

Art. no.	DN	d _ø mm	D cm	La (+/-) mm	L cm	Z cm
33938	50	54	7	18	17.6	10.6
33939	65	76.1	8.8	22	26.2	15.6
33940	80	88.9	11.7	23	28.6	16.6
33941	100	108	13.7	23	54.2	39.2

These articles are suitable for the following system: **Geberit Mapress Therm**

33932	12	15	2.6	7	15.1	11.1
33933	15	18	2.6	7	14.7	10.7
33934	20	22	3.1	11	10.6	6.4
33935	25	28	3.9	13	12	7.4
33936	32	35	4.6	13	13.9	8.7
33937	40	42	5.9	13	14.9	8.9
33938	50	54	7	18	17.6	10.6
33939	65	76.1	8.8	22	26.2	15.6

Art. no.	DN	d, ø mm	D cm	La (+/-) mm	L cm	Z cm
33940	80	88.9	11.7	23	28.6	16.6
33941	100	108	13.7	23	54.2	39.2