




used for: D-SUB



POS.	A -0.76	B +0.25	C	D -0.3	PART-NO.
9	31.19	16.79	25.00 +0.12/-0.13	6.12	DLS1XP5AK40X
15	39.52	25.12	33.30 +0.15/-0.1	6.12	DLS2XP5AK40X
25	53.42	38.84	47.04 ±0.13	5.99	DLS3XP5AK40X
37	69.70	55.30	63.50 ±0.13	5.99	DLS4XP5AK40X



NOTES:

- (b) 1. METAL SHELLS: STEEL; NICKEL PLATED
2. INSULATORS: PA UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. PCB-CLIP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
5. P.C.B. HOLE DRILLINGS SEE SHEET 2
6. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			scale:	
				2005	date		material:	
				drawn	27.06.	Lehmenkühler	title:	
				appd.	27.06.	Kühle		
				norm	DIN 41652			
				d-old			dwg no:	
1 x b	Ä 5865	29.10.2015	Unkrüer			16K1A1438	DIN-A 3 sh: 1/1	
a	Original							
rev.	description	date	name			part no:	SEE TABLE	

RoHS Compliant



rev.	description	date	name



title:	
P.C.B HOLE DRILLINGS	
D-SUB MALE 90° 9-37pos. pin angled 0.318inch stamped contacts - with threaded lock and clip	
dwg no:	DIN-A
16K1A1438	3
	sh: 1/1
part no: SEE SHEET 1	