

Eaton 135647

Catalog Number: 135647

Eaton Moeller® series E58 Retroflective sensing sensor, Sn=4500mm, 4L, 10-30VDC, NPN, PNP, M18, insulated material, line 2m 14101A6517

General specifications



Product Name

Eaton Moeller® series E58
Retroreflective sensor

Catalog Number

135647

EAN

4015081324408

Product Length/Depth

67.06 mm

Product Height

19.05 mm

Product Width

11.94 mm

Product Weight

0.18 kg

Certifications

UL 508

CE

UL Category Control No.: NRKH, NRKH7

CSA

IEC/EN 60947-5-2

CSA File No.: 50513

CSA-C22.2 No. 14

CSA Class No.: 3211-07

UL

UL File No.: E117028

Product specifications

Type

Optical sensors

Features

Polarized light

Straight beam

Electric connection type

Cable

Enclosure material

Plastic

Enclosure type

Cylinder, screw-thread

Operating mode

Switching principle: Adjustable bright/dark switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Protection against polarity reversal

Short-circuit protection

Reflected-light beam

For combination with reflector

Voltage type

DC

Connection type

4-wire

2 m connection cable

Light type

Polarity free red light

Degree of protection

IP67

NEMA 6

Interface type

Other

LED indicator

Status indication of Switching state: Red LED

Resources

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Declarations of conformity

DA-DC-00004657.pdf

DA-DC-00004652.pdf

Drawings

eaton-proximity-switches-dimensions-002.eps

eaton-proximity-switches-dimensions-008.eps

eaton-proximity-switches-3d-drawing-004.eps

Installation instructions

IL05305002Z

mCAD model

DA-CS-90_28267_013

DA-CD-90_28267_013

Switch function type

Programmable/configurable

Load current

Max. 100 mA (Ie, PNP)

Max. 250 mA (Ie, NPN, 120 > 50°C)

Laser protection class

None

Shock resistance

100 g, Mechanical, Shock duration 3 ms

Optical surface material

Plastic

Output current (mA) - max

100 mA

Output current at protected output - max

0 mA

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at DC - max

30 V

Rated control supply voltage (Us) at DC - min

10 V

Rated switching distance (Sn)

4500 mm

Reflector distance - min

0 mm

Sensor height

0 mm

Sensor length

67 mm

Switching distance - max

0 mm

Switching voltage of OSSD at state high

0 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Light-/dark switching

Switching output type

PNP/NPN

Sensor material

Insulated material

Wavelength of the sensor

0 nm

Width sensor

0 mm

Product category

Comet Series

Response time

1 ms

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

18 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operational current (I_b) in the switched state at 24 V DC

30 A

Adjustment type

Manual adjustment



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia