



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKL XCKM XCKS
Associated body	ZCKMD31H29 ZCKLD37H7 ZCKS5H29 ZCKL8 ZCKL8H7 ZCKSD35H29 ZCKSD35 ZCKM5 ZCKS1H29 ZCKMD39 ZCKSD37H29 ZCKM6 ZCKSD37 ZCKM9 ZCKM5H7 ZCKMD31 ZCKLD31 ZCKS6H29 ZCKS8 ZCKM1H7 ZCKM8H29 ZCKL6 ZCKLD39H7 ZCKS7 ZCKS2H29 ZCKS8H29 ZCKLD39 ZCKSD31H29 ZCKS9H29

ZCKL6H7  
 ZCKM7H29  
 ZCKMD37H29  
 ZCKSD39H29  
 ZCKM7  
 ZCKSD39  
 ZCKLD37  
 ZCKL5  
 ZCKL1H7  
 ZCKMD35H29  
 ZCKMD39H7  
 ZCKMD37H7  
 ZCKL1  
 ZCKMD35H7  
 ZCKM9H29  
 ZCKM5H29  
 ZCKM8  
 ZCKM6H7  
 ZCKMD35  
 ZCKS5  
 ZCKLD31H7  
 ZCKS6  
 ZCKM1H29  
 ZCKL5H7  
 ZCKMD37  
 ZCKS7H29  
 ZCKLD35  
 ZCKM6H29  
 ZCKMD39H29  
 ZCKL7  
 ZCKLD35H7  
 ZCKM1  
 ZCKM7H7  
 ZCKL7H7  
 ZCKS1  
 ZCKMD31H7  
 ZCKS2  
 ZCKS9  
 ZCKSD31  
 ZCKM8H7

Movement of operating head	Rotary
Type of operator	Spring rod lever spring return (with metal rod)
Type of approach	Lateral approach, 2 directions

### Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Plastic

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------