

WR 3000MER

Code No.: T0053368899N



Benefits

- › Power unit, 3 channels with soldering iron WP 120, desoldering iron DSX 120 and hot air iron HAP 200
- › Large allround set for all repair jobs
- › Desoldering iron DSX 120 for horizontal applications



In addition we recommend:




Fume extraction devices



Preheating plates



Zubehoer




Soldering Tips



Technical Data

Dimensions W x D x H (mm)	280 x 240 x 103
Dimensions W x D x H (Inch)	11,02 x 9,45 x 4,06
Weight (ca) in kg	7.3
Voltage	230 V
Heating output	400 W
Channels	3
Temperature range (depends on tool) °C	50 - 550
Temperature range (depends on tool) °F	150 - 950
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperaturgenauigkeit Heißluft °C	tbd
Temperaturgenauigkeit Heißluft °F	tbd
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding	Via a 3.5 mm jack bush (initial state-hard-grounded)
Display	LCD
Zusätzliche Vakuumpumpe	Pick Up
Max. air flow rate l/min (depends on tool)	15
Capacity l/min	18
Max. vacuum	---
Interface	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE