

Label, can be removed - EML-RM (45X5)R - 0830538

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Label, can be removed, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 45 x 5 mm

The figure shows a version of the article

Why buy this product

- Stick-on device marking, removable
- Particularly suitable for temporary marking
- The labels cannot be reused following removal



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 720502
Weight per Piece (excluding packing)	312.7 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Length (b)	45 mm
Width (a)	5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (assembly)	15 °C
Recommended storage conditions	23 °C / 50% relative humidity. Storage in poly bags is recommended prior to processing.

General

Color	white
Components	free from silicone and halogen
Material	Polyester

Label, can be removed - EML-RM (45X5)R - 0830538

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2500
Number of individual labels per row	2
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5145274 THERMOMARK X1.1
	5146231 THERMOMARK X1.2
	5146257 THERMOMARK S1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

Label, can be removed - EML-RM (45X5)R - 0830538

Classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals


Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details



Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black
