

RF-12S1N8AA200 - Device connector front mounting



1607279

<https://www.phoenixcontact.com/in/products/1607279>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, angled fixed, Screw locking mechanism, M23, number of positions: 12, contact connection type: Socket, Axial O-ring, 4x Ø 3.2, shielded: yes, flange dimensions: 26 mm x 26 mm, number of positions: 12, connection method: Crimp connection, series: RF, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1242263

Commercial data

Item number	1607279
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	ABR
Product key	ABRAGM
GTIN	4046356268479
Weight per piece (including packing)	140.5 g
Weight per piece (excluding packing)	209.2 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Mounting

Mounting type	Front mounting
Mounting	4x Ø 3.2

Product properties

Product type	Circular connectors (device side)
Series	RF
Application	Signal
	Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Thread type	M23

Dimensions

Housing

Flange dimensions	26 mm x 26 mm
-------------------	---------------

Material specifications

Seal material	FPM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

Electrical properties

Contact

Contact diameter	1 mm
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

RF-12S1N8AA200 - Device connector front mounting



1607279

<https://www.phoenixcontact.com/in/products/1607279>

Connection method	Crimp connection
Contact connection type	Socket

Connector

Type	angled fixed
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m

1607279

<https://www.phoenixcontact.com/in/products/1607279>


Drawings

Dimensional drawing



Installation dimensions

Schematic diagram




Connector pin assignment

1607279

<https://www.phoenixcontact.com/in/products/1607279>

Dimensional drawing



Dimensional drawing

RF-12S1N8AA200 - Device connector front mounting



1607279

<https://www.phoenixcontact.com/in/products/1607279>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1607279>

	cUL Recognized Approval ID: E153698-20090723			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	5 A	20	-

	UL Recognized Approval ID: E153698-20090723			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	48 V	5 A	20	-

cULus Recognized				
-------------------------	--	--	--	--

RF-12S1N8AA200 - Device connector front mounting



1607279

<https://www.phoenixcontact.com/in/products/1607279>

Classifications

ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	891ed791-28c7-4124-b1bf-1654c627993c

RF-12S1N8AA200 - Device connector front mounting



1607279

<https://www.phoenixcontact.com/in/products/1607279>

Accessories

PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>

Plastic protective cap, M23, series: M23 PRO



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in