



ENGLISH

M12 Connectivity

4 Port Distribution Box - 4 x M12, 5 pole (2 signals per port) with removable home run cable

Stock No's 174-7824, 174-7825

Primary Features

LED indication for easy diagnostics

IP65, IP67 when leads inserted and tightened


Removable home run lead for easy installation and maintenance

UL and CSA approved

Available in home run cable lengths:

5 Metres (RS 174-7824)

10 Metres (RS 174-7825)



File No. E201820

IND. CONT. EQ 54PM

Use Class 2 Source Only

For use in NFPA 79 Applications only

Adapters providing field wiring means are available from the manufacturer.

Refer to manufacturers information.

Maximum surrounding air temperature rating: 40 °C

Standard(s) for Safety:


UL 508-Industrial Control Equipment

CSA C22.2 No. 142-M1987-Process Control Equipment




Wiring Schematic

174-7824, 174-7825



M12 Females 5-pole



Contact Layout

PIN 1	(+)
PIN 2	(NC)/(S2)
PIN 3	(-)
PIN 4	(NO)/(S1)
PIN 5	(Earth)
LED display	LED (green): Power / LED (yellow): (S1/S2)

Cable

Cable number	363
No./diameter of wires	8×0.34 + 3×0.75 mm ²
Wire isolation	PVC
C-track properties	2 Mio.



Cable *continued*

174-7824, 174-7825

Jacket Color	gray
Material (jacket)	PUR/PVC (UL/CSA)
Outer Ø	8.1 mm ±5%
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C
Color (jacket)	gray
Bend radius (fixed)	10 × outer Ø

Technical Data

Operating voltage	24 V DC ±25%
Housing	Plastic, flame retardant
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Material	PBT
Signal per port	2
Operating current per contact	max. 4 A
Total current	max. 8 A
Locking of ports	Screw thread M12 × 1 mm
Temperature range	-20...+80 °C
Dimensions H × W × D	100×50.2×17 mm