

# UCT-WMTBA (29X6) CUS - Cable marker



1014090

<https://www.phoenixcontact.com/in/products/1014090>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Sheet, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: > 6 mm, Number of individual labels: 15, text field height: 6 mm, text field width: 29 mm



## Your advantages

- The UCT-WMTBA ... UniCard labeling range includes markers that can be secured using standard cable binders
- Thanks to their angular shape the markers fit perfectly onto cables
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your requirements
- The format automatically ensures printing with a high degree of positioning accuracy

## Commercial data

Item number	1014090
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8
Product key	BG8138
Catalog page	Page 271 (NTK-2014)
GTIN	4046356781428
Weight per piece (including packing)	10.55 g
Weight per piece (excluding packing)	8.45 g
Customs tariff number	49119900
Country of origin	PL

# UCT-WMTBA (29X6) CUS - Cable marker



1014090

<https://www.phoenixcontact.com/in/products/1014090>

## Technical data

### Product properties

Product type	Labeled conductor marker
Type	Card form

### Marking

Number of individual labels	15
Number of individual labels per row	5

### Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

### Material specifications

Color	white (RAL 9010)
Material	PC
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Scratch test for the determining scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

#### Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h

# UCT-WMTBA (29X6) CUS - Cable marker



1014090

<https://www.phoenixcontact.com/in/products/1014090>

Rating 100 °C (121 °C)	Test passed
------------------------	-------------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
IRM 901	Test passed
IRM 902	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	ISO 22479:2019-05
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

## Dimensions

Width	8 mm
Text field width	29.00 mm
Text field height	6.00 mm
Length	29 mm

## External dimensions

Outside diameter	> 6 mm ... 136 mm
------------------	-------------------

# UCT-WMTBA (29X6) CUS - Cable marker



1014090

<https://www.phoenixcontact.com/in/products/1014090>

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Standards	
Standards/regulations	EN 45545-2

# UCT-WMTBA (29X6) CUS - Cable marker



1014090

<https://www.phoenixcontact.com/in/products/1014090>

## Classifications

### ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UCT-WMTBA (29X6) CUS - Cable marker



1014090  
<https://www.phoenixcontact.com/in/products/1014090>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)