

# Eaton 265927

Catalog Number: 265927

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 4p, 1250A, H4-4-AE1250



General specifications

| Product Name                                                    | Catalog Number |
|-----------------------------------------------------------------|----------------|
| Eaton Moeller series NZM molded case circuit breaker electronic | 265927         |
|                                                                 | EAN            |
|                                                                 | 4015082659271  |
| Product Length/Depth                                            | Product Height |
| 401 mm                                                          | 207 mm         |
| Product Width                                                   | Product Weight |
| 280 mm                                                          | 27 kg          |
| Compliances                                                     | Certifications |
| RoHS conform                                                    | IEC/EN 60947   |
|                                                                 | IEC            |

## Product specifications

### Type

Circuit breaker

### Special features

Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity  $I_{cn}$ )  
Rated current = rated uninterrupted current: 1250 A  
Set value in neutral conductor is synchronous with set value  $I_r$  of main pole.  
R.m.s. value measurement and "thermal memory"

### Application

Use in unearthed supply systems at 525 V

### Amperage Rating

1250 A

### Voltage rating

690 V - 690 V

### Circuit breaker frame type

NZM4

### Features

Motor drive optional  
Protection unit

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

## Resources

### Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-047.eps](#)

### Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-023.eps](#)

### eCAD model

[ETN.265927.edz](#)

### Installation instructions

[eaton-circuit-breaker-basic-unit-nzmn4-il01210010z.pdf](#)

### Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

### mCAD model

[DA-CD-nzm4\\_4p](#)

[DA-CS-nzm4\\_4p](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

##### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

##### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

##### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Pollution degree

3

#### Mounting Method

Built-in device fixed built-in technique

Fixed

#### Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

#### Equipment heat dissipation, current-dependent

173.44 W

#### Utilization category

A (IEC/EN 60947-2)

#### Isolation

500 V AC (between auxiliary contacts and main contacts)

300 V AC (between the auxiliary contacts)

#### Ambient operating temperature - max

70 °C

#### Ambient operating temperature - min

-25 °C

#### Ambient storage temperature - max

70 °C

#### Ambient storage temperature - min

40 °C

#### Number of auxiliary contacts (change-over contacts)

0

#### Number of auxiliary contacts (normally closed contacts)

0

#### Number of auxiliary contacts (normally open contacts)

0

#### Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part

110

#### Degree of protection

IP20 (basic degree of protection, in the operating controls area)

IP20

#### Direction of incoming supply

As required

#### Electrical connection type of main circuit

Screw connection

#### Current rating of neutral conductor

200% of phase conductor

#### Lifespan, mechanical

10000 operations

#### Overvoltage category

III

#### Degree of protection (IP), front side

IP66 (with door coupling rotary handle)

IP40 (with insulating surround)

#### Degree of protection (terminations)

IP10 (tunnel terminal)

IP00 (terminations, phase isolator and strip terminal)

#### Number of poles

Four-pole

#### Terminal capacity (copper strip)

Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor terminal

Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal

Min. 5 segments of 25 mm x 1 mm at rear-side connection (punched)

10 segments of 80 mm x 1 mm (2x) at rear-side width extension

10 segments of 50 mm x 1 mm (2x) at 1-hole module plate

Max. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched)

#### Lifespan, electrical

2000 operations at 400 V AC-3

1000 operations at 690 V AC-3

3000 operations at 415 V AC-1

2000 operations at 415 V AC-3

2000 operations at 690 V AC-1

3000 operations at 400 V AC-1

#### Functions

System and cable protection

#### Shock resistance

15 g (half-sinusoidal shock 11 ms)

#### Position of connection for main current circuit

Front side

#### Rated operational current for specified heat dissipation (I<sub>n</sub>)

1250 A

#### Release system

Electronic release

#### Short-circuit total breaktime

< 25 ms ( < 415 V); < 35 ms (> 415 V)

#### Rated short-time withstand current (t = 0.3 s)

19.2 kA

#### Rated short-time withstand current (t = 1 s)

19.2 kA

#### Short-circuit release non-delayed setting - max

15000 A

#### Short-circuit release non-delayed setting - min

2500 A

#### Terminal capacity (control cable)

0.75 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (2x)

0.75 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1x)

#### Terminal capacity (copper busbar)

Min. 25 mm x 5 mm direct at switch rear-side connection

Max. 50 mm x 10 mm (2x) direct at switch rear-side connection

Min. 25 mm x 5 mm at rear-side 1-hole module plate

50 mm x 10 mm (2x) at rear-side 2-hole module plate

M10 at rear-side screw connection

Max. 80 mm x 10 mm (2x) at rear-side width extension

Min. 60 mm x 10 mm at rear-side width extension

Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate

#### Terminal capacity (copper solid conductor/cable)

35 mm<sup>2</sup> - 185 mm<sup>2</sup> (4x) at rear-side 2-hole module plate

95 mm<sup>2</sup> - 185 mm<sup>2</sup> (2x) at rear-side 2-hole module plate

95 mm<sup>2</sup> - 240 mm<sup>2</sup> (6x) at rear-side width extension

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (4x) at 4-hole tunnel terminal

300 mm<sup>2</sup> (4x) at rear-side width extension

120 mm<sup>2</sup> - 300 mm<sup>2</sup> (1x) at rear-side 1-hole module plate

95 mm<sup>2</sup> - 300 mm<sup>2</sup> (2x) at rear-side 1-hole module plate

#### Terminal capacity (aluminum solid conductor/cable)

70 mm<sup>2</sup> - 185 mm<sup>2</sup> (2x) at rear-side 1-hole module plate

185 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x) at rear-side 1-hole module plate

50 mm<sup>2</sup> (4x) at rear-side 2-hole module plate

70 mm<sup>2</sup> - 240 mm<sup>2</sup> (6x) at rear-side width extension

240 mm<sup>2</sup> (2x) at rear-side width extension

**Terminal capacity (copper stranded conductor/cable)**

120 mm<sup>2</sup> - 185 mm<sup>2</sup> (1x) direct at switch rear-side connection

50 mm<sup>2</sup> - 185 mm<sup>2</sup> (4x) direct at switch rear-side connection

**Terminal capacity (aluminum stranded conductor/cable)**

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (4x) at 4-hole tunnel terminal

**Handle type**

Rocker lever

**Short delay current setting (I<sub>sd</sub>) - max**

0 A

**Short delay current setting (I<sub>sd</sub>) - min**

0 A

**Instantaneous current setting (I<sub>i</sub>) - max**

15000 A

**Instantaneous current setting (I<sub>i</sub>) - min**

2500 A

**Number of operations per hour - max**

60

**Overload current setting (I<sub>r</sub>) - max**

1250 A

**Overload current setting (I<sub>r</sub>) - min**

630 A

**Overload current setting (I<sub>r</sub>)**

630 A - 1250 A

**Rated short-circuit breaking capacity I<sub>cs</sub> (IEC/EN 60947) at 230 V, 50/60 Hz**

63 kA

**Rated short-circuit breaking capacity I<sub>cs</sub> (IEC/EN 60947) at 400/415 V, 50/60 Hz**

50 kA

**Rated short-circuit breaking capacity I<sub>cs</sub> (IEC/EN 60947) at 440 V, 50/60 Hz**

50 kA

**Rated short-circuit breaking capacity I<sub>cs</sub> (IEC/EN 60947) at 525 V, 50/60 Hz**

50 kA

**Rated short-circuit breaking capacity I<sub>cs</sub> (IEC/EN 60947) at 690 V, 50/60 Hz**

37 kA

**Rated short-circuit making capacity I<sub>cm</sub> at 400/415 V, 50/60 Hz**

187 kA

Rated short-circuit making capacity Icm at 440 V, 50/60 Hz

187 kA

Rated short-circuit making capacity Icm at 525 V, 50/60 Hz

143 kA

Rated short-circuit making capacity Icm at 690 V, 50/60 Hz

100 kA

#### Standard terminals

Screw terminal

#### Optional terminals

Connection on rear. Strip terminal. Tunnel terminal

Rated short-circuit making capacity Icm at 240 V, 50/60 Hz

275 kA

Rated impulse withstand voltage (Uimp) at auxiliary contacts

6000 V

Rated impulse withstand voltage (Uimp) at main contacts

8000 V

Rated insulation voltage (Ui)

1000 V AC



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia