



MY4IN-D2-GS-R DC24

Relay, plug-in, 14-pin, 4PDT, 6 A, mechanical & LED indicators, Coil Surge Absorption, lockable push test button, 24 VDC

Specifications

Mounting method	With plug-in socket
Usage	General purpose
Poles	4
Rated carry current	6 A
Coil voltage	24 V
Operation voltage	DC
Contact material	Ag
Contact description	4PDT
Features	Diode, LED, Test button, Transparent case, With mechanical indicator
Terminal type	Plug-in, Solder

Fits to



PY14-02

Socket, back-connecting,
14-pin, PCB terminals



PYF-14-PU

Socket, DIN rail/surface
mounting, 31 mm, 14-pin,
Push-in terminals



PYF-14-PU-L

Socket, DIN rail/surface
mounting, 31 mm, 14-pin,
Push-in terminals,



PYF14-ESN-B

Socket, with common and
coil terminals on the bottom
and with the NC & NO
terminal on the top - Black.



PYF14-ESS-B

Socket, with coil terminals
on the bottom and with the
common and NC & NO
terminals on the top - Black.



PYF14A-N

Socket, DIN rail/surface
mounting, 14-pin, screw
terminals (IEC/VDE)



PYF14S

Socket, DIN rail mounting,
14-pin, screwless terminals



PYFZ-14-E

Socket, DIN rail/surface
mounting, 14-pin, screw
terminals (standard)

Downloads



Industrial Relays Brochure

EN PDF 2.77 MB



MY-GS- R/MY(s)/MYK/MYQ/MYH Miniature Power Relays

Datasheet

EN PDF 20.3 MB



OMRON Manufacturing Know-How: High Quality Relays

Leaflet

EN PDF 449 KB



Solution case study No.8 Environment resistance

Brochure

EN PDF 623 KB

