

FEATURES

- Made from durable fabricated 316 stainless steel
- Durable welded construction
- Provides protection against corrosive media
- Reduces the possibility of contamination
- Protection against physical impact such as clinker in a furnace
- Allows quick and easy removal and insertion of the probe from the process
- Prevents spillage and the need to drain vessels and pipes
- Supplied with 1/8 BSP stainless steel compression fitting

RS PRO Thermowell for use with Temperature Sensor With 6mm Probe Diameter, 1/2 BSP

RS Stock No.: 286-923



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Temperature Sensor Accessories



Product Description

From RS PRO a high-quality thermowell for protecting your industrial temperature probe or thermocouple from damage. This damage is can be caused by the harsh processes the sensor is inserted into such as corrosive media. Thermowells also allow your temperature probe to be easily removed and interchanged without the need to open up and disturb the process. This thermowell is also called a thermopocket as it has a welded, fabricated 316 stainless steel design as opposed to being machined from solid metal and is suitable for use in low-pressure environments.

General Specifications

Accessory Type	Thermowell
For Use With	Temperature Sensor
Applications	1/2 BSP Connector

Mechanical Specifications

Connector Size	1/2"BSP Parallel
Immersion Length	150mm
Pocket Diameter	11.1mm
C/W fitting	Yes
To Suitable	6.0mm


Approvals

Compliance/Certifications	RoHS
---------------------------	------

Temperature Sensor Accessories







Temperature Sensor Accessories



Suits probe DiaØ	Process Thread	*Immersion Length 'L'	Pocket Dia 'D'	C/W fitting /to suit	Allied Code	RS order Code
6.0mm	1/2"BSP Parallel	25mm	11.1mm	Yes/6.0mm		178-0956
6.0mm	1/2"BSP Parallel	50mm	11.1mm	Yes/6.0mm		178-0957
6.0mm	1/2"BSP Parallel	75mm	11.1mm	Yes/6.0mm		178-0958
6.0mm	1/2"BSP Parallel	100mm	11.1mm	Yes/6.0mm	70643613	363-3007
6.0mm	1/2"BSP Parallel	150mm	11.1mm	Yes/6.0mm	70637837	286-923
6.0mm	1/2"BSP Parallel	350mm	11.1mm	Yes/6.0mm	70637838	286-939
6.0mm	1/2"BSP Parallel	550mm	11.1mm	Yes/6.0mm	70637839	286-945
3.0mm	1/2"BSP Parallel	25mm	8.0mm	Yes/3.0mm		178-0953
3.0mm	1/2"BSP Parallel	50mm	8.0mm	Yes/3.0mm		178-0954
3.0mm	1/2"BSP Parallel	75mm	8.0mm	Yes/3.0mm		178-0955
3.0mm	1/2"BSP Parallel	100mm	8.0mm	Yes/3.0mm	70643614	363-3029
3.0mm	1/2"BSP Parallel	150mm	8.0mm	Yes/3.0mm	70643615	363-3035

Solid drilled Thermowell (standard parallel type)



Suits probe	Process Thread	*Immersion	Pocket	C/W fitting	Allied	RS order
DiaØ		Length	Dia	/to suit	Code	Code
6.0mm	1/2"BSP Parallel	150mm	12mm	Yes/6.0mm	70643385	338-9508

^{*}To allow full insertion of probe into pocket then length of probe to be used should be a minimum of 50mm longer than immersion length shown Solid drilled Thermowells — Tapered (high pressure tapered type)



Suits probe DiaØ	Process Thread	*Immersion Length 'L'	Pocket Dia	C/W fitting /to suit	Allied Code	RS order Code
6.0mm	1/2"BSP Parallel	100mm	16/12mm	Optional	70644132	436-0665
6.0mm	1/2"BSP Parallel	150mm	16/12mm	Optional	70644133	436-0671