

Eaton 187066

Catalog Number: 187066

Eaton Moeller® series M30 Key-operated actuator, Flat Front, maintained, 2 positions 0, I, Metal bezel, Suitable for master key systems



General specifications

Product Name	Catalog Number
Eaton Moeller® series M30 Key-operated actuator	187066
Product Length/Depth	36 mm
Product Height	Product Width
75 mm	46 mm
Product Weight	Certifications
0.085 kg	VDE 0660
	IEC/EN 60947
	CSA file No. 012528
	CSA Class No.: 3211-03
	DNV
	UL File No.: E29184
	GL
	IEC/EN 60947-5
	UL 508
	CSA-C22.2 No. 14-05
	CSA-C22.2 No. 94-91
	CE marking
	UL Category Control No.: NKCR
	UL Listed
	CSA certified

Features & Functions

Bezel color

Titanium

Bezel material

Metal

Design

Key operation lock mechanism

Flat front

Fitted with:

Front ring

General

Accessories

2 keys included with supplied equipment.

Degree of protection

NEMA 4X, 13

Degree of protection (front side)

IP66

Lifespan, mechanical

100,000 Operations

Opening diameter

30 mm

Operating frequency

100 Operations/h

Operating torque

0.5 Nm

Overvoltage category

III

Pollution degree

3

Product category

RMQ-Titan

Size

Front dimensions: Ø 36 mm

Suitable for

Master key systems

Switching angle

60 °

Type

Key-operated button

Ambient conditions, mechanical

Mounting position

As required

Shock resistance

Mechanical, According to IEC/EN 60068-2-27

15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal

Climatic environmental conditions

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

70 °C

shock 11 ms

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Communication

[Connection to SmartWire-DT](#)

With SWD-RMQ connections

Yes

Actuator

Actuator color

Black

Actuator function

Maintained

Switching function latching

Key withdrawable in position 1

Key withdrawable in position 0

Actuator type

Key

Number of switch positions

2

Contacts

[Force for positive opening - min](#)

0 N

Design verification

[Equipment heat dissipation, current-dependent Pvid](#)

0 W

[Heat dissipation capacity Pdiss](#)

0 W

[Heat dissipation per pole, current-dependent Pvid](#)

0 W

[Rated operational current for specified heat dissipation \(In\)](#)

0 A

[Static heat dissipation, non-current-dependent Pvs](#)

0 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

Resources

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

[Flip catalog - Product Range Catalog - Command and indication](#)

Drawings

[eaton-operating-m30-key-operated-actuator-dimensions-002.eps](#)

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-m30-dimensions-006.eps](#)

[eaton-operating-m30-key-operated-actuator-3d-drawing-002.eps](#)

[eaton-general-approval-m22-symbol.eps](#)

[eaton-general-m22-symbol.eps](#)

eCAD model

[ETN.187066.edz](#)

Installation instructions

[eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf](#)

Installation videos

[RMQ Flat Design](#)

mCAD model

[DA-CS-schluesseltaste_sa_flatfront](#)

[DA-CD-schluesseltaste_sa_flatfront](#)

Multimedia

[MCI Multicolor Light Indicator M22 with SmartWire-DT](#)

[easyE4 SmartWire-DT module with Remote Touch Display and RMQ multi color indicator](#)

[RMQ small E-Stop emergency-stop button](#)

[MCI MultiColor Light Indicator RMQ compact solution](#)

Sales notes

[eaton-control-circuit-devices-rmq-titan-fl144090en-en-us.pdf](#)

[eaton-rmq-small-e-stop-flyer-fl047006en-en-us.pdf](#)

[eaton-rmq-flat-enclosure-flyer-fl047003en-en-us.pdf](#)

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

System overview

[Pilot devices - selection aid](#)

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)