

特点

- 不锈钢
- 头高度等于柄直径
- 成本效益、比钛合金要高
- 提供各种螺纹尺寸
- 高质量螺纹设计

RS M5 Pro 10mm 内六角半圆头螺钉、本色 不锈钢

RS 号: 183-8660



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与领先品牌相当的质量、而无需支付高昂的价格。

商品描述属性

RS PRO 推出种类多样的半圆头凹头螺钉系列。由高质量不锈钢制成，并利用六角头实现简单有效的安装。这些螺钉适用于多种应用，如机器维修或建筑。优质的凹头螺钉具有耐久、坚固的结构，您可以放心使用。所有型号均高度可靠且质量极佳

一般规格

螺纹尺寸	M5
头部形状	六角套筒按钮
材料	不锈钢
表面	普通
螺纹类型	公制
应用	木材加工、家用应用、紧固件和固定件、机器工具和维修、安全防护、面板制造

机械规格

长度	10mm
不锈钢类型	304 A2
螺距	0.8mm
头直径范围	9.14mm 至 9.50mm
头部高度范围	2.50mm 至 2.75mm
钥匙尺寸标称范围	3.02mm 至 3.071mm
关键敬业度	1.56
螺纹公差	6g

认证

合规性 / 认证


rohs 符合性证书, ISO7380 , ansi B18



Please view our full range listing below for all A2, 304 Stainless Steel Self-Colour Hexagon Socket Button Head Screws

Head Shape	Material	Stainless Steel Type	Thread Size	Length	RS Part No.
Hex Socket Button	Stainless Steel	A2, 304	M3	8 mm	1838597
Hex Socket Button	Stainless Steel	A2, 304	M3	10 mm	1838604
Hex Socket Button	Stainless Steel	A2, 304	M3	12 mm	1838610
Hex Socket Button	Stainless Steel	A2, 304	M4	8 mm	1838626
Hex Socket Button	Stainless Steel	A2, 304	M4	10 mm	1838632
Hex Socket Button	Stainless Steel	A2, 304	M4	12 mm	1838648
Hex Socket Button	Stainless Steel	A2, 304	M4	16 mm	1838654
Hex Socket Button	Stainless Steel	A2, 304	M5	10 mm	1838660
Hex Socket Button	Stainless Steel	A2, 304	M5	12 mm	1838676
Hex Socket Button	Stainless Steel	A2, 304	M5	16 mm	1838698
Hex Socket Button	Stainless Steel	A2, 304	M5	20 mm	1838705
Hex Socket Button	Stainless Steel	A2, 304	M5	25 mm	7976092
Hex Socket Button	Stainless Steel	A2, 304	M6	10 mm	7976096
Hex Socket Button	Stainless Steel	A2, 304	M6	12 mm	1838711
Hex Socket Button	Stainless Steel	A2, 304	M6	16 mm	1838727
Hex Socket Button	Stainless Steel	A2, 304	M6	20 mm	1838733
Hex Socket Button	Stainless Steel	A2, 304	M6	25 mm	1838755
Hex Socket Button	Stainless Steel	A2, 304	M6	30 mm	7976106
Hex Socket Button	Stainless Steel	A2, 304	M6	40 mm	7976109

Hex Socket Button	Stainless Steel	A2, 304	M8	12 mm	1838761
Hex Socket Button	Stainless Steel	A2, 304	M8	16 mm	1855794
Hex Socket Button	Stainless Steel	A2, 304	M8	20 mm	1838777
Hex Socket Button	Stainless Steel	A2, 304	M8	25 mm	1838783
Hex Socket Button	Stainless Steel	A2, 304	M8	30 mm	7976103
Hex Socket Button	Stainless Steel	A2, 304	M8	40 mm	7976112
Hex Socket Button	Stainless Steel	A2, 304	M8	50 mm	7976115



~ISO 7380			ANSI B 18.3.4M	
Material	Steel	Stainless Steel	Material	Steel
Property Class	10.9	A2 & A4	Property Class	12.9
Finish	Furnace Black	Plain	Finish	Furnace Black
Thread Tolerance	6g	6g	Thread Tolerance	4g6g

第页 5 的 5