

FEATURES

- ABS (acrylonitrile butadiene styrene) plastic body
- Grey in colour
- External dimensions of 231 mm x 212 mm x 67 mm
- Maximum PCB size of 200 mm x 197 mm (horizontally mounted) or 203 mm x 57 mm (vertically mounted)
- EMI / RFI shielded
- Restriction of Hazardous Substances (RoHS) certified
- Non-ventilated
- No carrying handle

RS PRO Grey ABS Instrument Case, 231 x 212 x 67mm

RS Stock No.: 284-6511



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

This RS PRO project box is designed to shield your electronics from electromagnetic interference (EMI) and radio-frequency interference (RFI). It can be used to house electronic components while offering excellent protection. Made from ABS (acrylonitrile butadiene styrene) plastic, the box boasts a high resistance to corrosive chemicals and physical impact. Lightweight but durable, it has moulded bosses for PCB mounting, with additional slots for chassis rail mounting. The maximum PCB size accepted by this box is 200 mm by 197 mm when mounted horizontally, or 203 mm by 57 mm when mounted vertically.

General Specifications

Body Material	ABS
Base Material	ABS
Colour	Grey
Ventilated	No
Carrying Handle	No
Application	Benchtop test equipment, medical analysers and industrial control systems.

Mechanical Specifications

External Length	231mm
External Width	212mm
External Height	67mm
External Dimensions	231mm x 212mm x 67mm

Approvals

Standards Met	RoHS
---------------	------

Instrument Cases





