

## ZCMD39L5

limit switch body ZCMD - 2NC+1NO - silver - snap action - connection - 5 m



[Download your ZCMD39L5 datasheet](#)



[Characteristics](#) | [Documents & Downloads](#)

### Main

Hide

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch body
Device short name	ZCMD
Design	Miniature
Body type	Fixed
Associated head	ZCE01 ZCE02 ZCE06 ZCE07 ZCE08 ZCE09 ZCE10 ZCE11 ZCE13 ZCE14 ZCE21 ZCE24 ZCE27 ZCE28 ZCE29 ZCE62 ZCE63 ZCE64 ZCE65 ZCE66 ZCE67 ZCEF0 ZCEF2 ZCEG1
Body material	Zamak
Number of poles	3
Contacts type and composition	2 NC + 1 NO
Contacts operation	Snap action

### Complementary

Hide



Product compatibility	XCMD
Electrical connection	Removable cable
Cable length	5 m
Cable composition	7 x 0.5 mm <sup>2</sup>
Wire insulation material	PvR
Contacts insulation form	Zb
Contacts material	Silver plated contacts
Positive opening	With
Minimum actuation speed	0.01 m/min
[Ui] rated insulation voltage	300 V degree of pollution 3 conforming to UL 508 400 V degree of pollution 3 conforming to IEC 60947-5-1 300 V degree of pollution 3 conforming to CSA C22.2 No 14

<b>Resistance across terminals</b>	< 25 mOhm conforming to IEC 60255-7 category 3
<b>[Uimp] rated impulse withstand voltage</b>	4 kV conforming to IEC 60664 4 kV conforming to IEC 60947-1
<b>Short circuit protection</b>	6 A by gG cartridge fuse
<b>Electrical durability</b>	5000000 cycles, DC-13 120 V, 1 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 24 V, 3 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 2 W, operating rate: < 60 cyc/mn, load factor: 0.5 conforming to IEC 60947-5-1 appendix C
<b>Width</b>	30 mm
<b>Height</b>	50 mm
<b>Depth</b>	16 mm
<b>Product weight</b>	0.065 kg

## Environment - Hide

<b>Ambient air temperature for storage</b>	-40...70 °C
--	-------------

## Offer Sustainability - Hide

<b>Sustainable offer status</b>	Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 1001 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available  <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Available  <a href="#">download End of life manual</a>

## Contractual warranty - Hide

<b>Period</b>	18 months
---------------	-----------