



Part Number : [1200878468](#)
Product Description : Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm² PVC Cable, 5.0m (16.40') Length
Series Number : 120087
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 484030E02M050



Documents & Resources

Drawings
[1200878468_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm ² PVC Cable, 5.0m (16.40') Length
IP Rating	IP68
Product Name	Micro-Change (M12), Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	78172532424

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	N/A
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	None

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	174.458/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A