

Through-type terminal thermoplast Screw terminal on both sides Single terminal, orange, 6mm, Sz. 2.5



Model	
product brand name	SETRON
product designation	Terminal blocks
design of the product	through-type terminal
product variations	through-type terminal, for mounting on mounting rail acc. to IEC 60715
design of terminal terminal levels internally linked	No
General technical data	
terminal contact spacing	6 mm
operating voltage rated value	800 V
Protection class	
combustibility class according to UL 94	V2
Main circuit	
operational current rated value	24 A
Appearance	
color	orange
Product details	
product component required end cover plate	No
Number	
number of terminal levels	1
number of terminal points per terminal level	2
Connections	
stripped length	11 mm
connectable conductor cross-section solid	
• minimum	2.5 mm <sup>2</sup>
• maximum	2.5 mm <sup>2</sup>
connectable conductor cross-section stranded	
• minimum	2.5 mm <sup>2</sup>
• maximum	2.5 mm <sup>2</sup>
connectable conductor cross-section finely stranded	
• with core end processing minimum	2.5 mm <sup>2</sup>
• with core end processing maximum	3 mm <sup>2</sup>
• without core end processing minimum	2.5 mm <sup>2</sup>
• without core end processing maximum	2.5 mm <sup>2</sup>
tightening torque with screw-type terminals	
• minimum	0.5 N·m
• maximum	1 N·m
type of connection 1	screw-type terminal
type of connection 2	screw-type terminal
position of the terminal	lateral
Mechanical Design	

height with lowest-profile installation	26 mm
length	41 mm
fastening method	DIN rail 35 mm
net weight	7 g
material of the insulating body	Thermoplast

#### Environmental conditions

ambient temperature during operation	
• minimum	-25 °C
• maximum	55 °C

#### Approvals Certificates

General Product Approval	Declaration of Con- formity	other
--------------------------	--------------------------------	-------

[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

#### Environment

[Environmental Con-  
firmations](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WA1011-1BF22>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WA1011-1BF22>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8WA1011-1BF22](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA1011-1BF22)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/20/2023

