

RAD-CAB-PFP600-25 - Antenna cable



5606126
<https://www.phoenixcontact.com/in/products/5606126>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable, outside diameter: 15 mm (0.6 in.), inner conductor: solid, attenuation: 1.0 / 1.3 / 2.0 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2x N (male), cable length: 7.5 m (25 ft.)



Your advantages

- Low attenuation
- UV resistant
- For outdoor installation

Commercial data

Item number	5606126
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC6A3
Catalog page	Page 397 (C-6-2019)
GTIN	4046356683937
Weight per piece (including packing)	2,200 g
Weight per piece (excluding packing)	1,677 g
Country of origin	CN

RAD-CAB-PFP600-25 - Antenna cable



5606126

<https://www.phoenixcontact.com/in/products/5606126>

Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Coaxial cable

Electrical properties

Frequency range

400 MHz ... 5.8 GHz

Impedance

50 Ω

Connection data

Connector connection

Connection method

N (male)

Notes

Both sides

Cable/line

Cable length

7.5 m

Cable type

PFP-600

External sheath, color

black

868 / 900 MHz

1 dB

2.4 GHz

1.3 dB

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-40 °C ... 85 °C

Ambient temperature (storage/transport)

-40 °C ... 70 °C

RAD-CAB-PFP600-25 - Antenna cable



5606126

<https://www.phoenixcontact.com/in/products/5606126>

Classifications

ECLASS

ECLASS-11.0	27060310
ECLASS-12.0	27060310
ECLASS-13.0	27060310

ETIM

ETIM 9.0	EC001682
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

RAD-CAB-PFP600-25 - Antenna cable



5606126

<https://www.phoenixcontact.com/in/products/5606126>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cbaa8f2e-cbef-4c71-bffe-dfca3f8241b9

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in