

## FEATURES

- **Natural Rubber Material:** Provides excellent flexibility and vibration absorption
- **Threaded Stud Mount Type:** Ensures secure and straightforward installation
- **Compression Load of 2000 N:** Handles substantial loads effectively
- **Shore A 70 Hardness:** Balances durability with flexibility
- **Wide Operating Temperature Range (-40 °C to 80 °C):** Suitable for various environments
- **RoHS Compliant:** Meets safety and environmental standards

## RS PRO Male Buffer Foot Anti-Vibration Mount, 25 mm Bore

RS Stock No: 715-073



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO anti-vibration mount is designed to reduce noise and vibration in machinery and equipment. It features a male buffer foot with a threaded stud for easy installation. The primary benefit is its ability to enhance equipment longevity by minimizing wear and tear.

## General Specifications

Anti Vibration Mount Type	Male Buffer Foot
Bore Length	25 mm
Bore Size	8 mm
Compression Deflection	10 mm
Compression Load	2000 N
Foot Colour	Black
Foot Height	40 mm
Foot Shape	Cylindrical
Mount Type	Threaded Stud
Product Type	Anti-Vibration Mount
Shore Hardness	Shore A 70
Thread Size	M8

## Mechanical Specifications

Material	Natural Rubber
Outside Diameter	30 mm
Overall Height	90 mm

## Operation Environment Specifications

Maximum Operating Temperature	80 °C
Minimum Operating Temperature	-40 °C

## Approvals

Standards/Approvals	RoHS
---------------------	------