



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **2**
Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	1a,1b
Number of Positions	2
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Locking Latch Between Cavity Number	1&2
Panel Mount Feature	Without
Mating Retention Type	Latch
PCB Mount Retention	Without
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Connector Height	13.9 mm[.547 in]
Connector Length	25.5 mm[1 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

RAST Version	None
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Glow Wire

Packaging Features

Packaging Method	Package
Packaging Quantity	3200

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)





Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 3-1241961-1 2POS STANDARD TIMER HOUSING	 TE Part # 9-1241961-2 STD TIM HOUSING MKII 2POS	 TE Part # 2-1241961-7 STD TIM HOUSING MKII 3POS	 TE Part # 1241961-1 STD TIM HOUSING MKII 2POS
 TE Part # 1241961-3 STD TIM HOUSING MKII 2POS	 TE Part # 5-1241983-3 STANDARD TIMER HOUSING MARK II	 TE Part # 8-1241961-2 STD TIM HOUSING MKII 2POS	 TE Part # 8-1241961-3 2POS STD-TIMER HOUSING PITCH5 MK II
 TE Part # 4-1241961-3 2POS.STD.TIMER HSG.MARK II	 TE Part # 2178561-2 STD-TIM GEH 2P_V0-GWT	 TE Part # 6-1241961-3 STD TIM HOUSING MKII 2POS	 TE Part # 964768-2 STD-TIM HSG SPECIAL 2P (GREY)



TE Part # 6-1241961-2
STD TIM HOUSING MKII 2POS

TE Part # 7-1241961-2
STD TIM HOUSING MKII 2POS

TE Part # 964768-3
STD-TIM HSG SPECIAL 2P (NATURE)

Also in the Series | RAST 5 IDC Connectors

Connector Contacts(12)

Crimp Terminal Housings(39)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(417)

Power Contacts(3)

Rectangular Power Connectors(481)

Standard Edge Connectors(31)

Wire-to-Board Headers & Receptacles (417)

Customers Also Bought

TE Part #1-172165-2
2CIR MINI U-M-N-L PLUG RED

TE Part #1-1863003-2
UMN 9WAY PLUG HOUSING

TE Part #180430-2
250 FASTON, FLAG, REC., 20-16 AWG, TPBR


TE Part #2178473-3
3POS UMN PLUG HSG GW

TE Part #926869-1
UNIV.M-N-L SOCKET

TE Part #1-1703062-2
CAP, 2 CIRCUIT, UNIVERSAL MATE-N-LOK

TE Part #171637-1
MINI U-M-N-L SOCKET CONTACT

TE Part #1-1703061-2
PLUG, 2 CIRCUIT, UNIVERSAL MATE-N-LOK



Documents

Product Drawings

STD TIM HOUSING MKII 2POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1241961-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1241961-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1241961-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Product Specification

German

Agency Approvals

VDE Certificate

English