

1-332070-1 ✓ ACTIVE



TE Internal #: 1-332070-1

3.63 mm [.143 in] Socket Length, 1.83 mm [.072 in] PCB Hole,
Closed Bottom, .653 mm² Wire, 19 AWG, Cable-to-Board, Power &
Signal, Pin Sockets

[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 6.5A



Socket Length: 3.63 mm [.143 in]

PCB Hole Diameter: 1.83 mm [.072 in]

Socket Sleeve Style: Closed Bottom

Wire Size: 19 AWG

[All Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 6.5A \(10\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Closed Bottom
Connector System	Cable-to-Board
Sealable	No

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Plating Material	Gold Flash over Nickel
Sleeve Material	Copper

Contact Features

Contact Spring Plating Material	Gold
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	30 μm[30 μin]
Contact Spring Plating Thickness	.762 μm[30 μin]



Contact Current Rating (Max)	6.5 A
------------------------------	-------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Insertion Method	Hand/Semi-Automatic
Termination Method to Wire & Cable	Solder

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.031 – .125 in]
Socket Length	3.63 mm [.143 in]
PCB Hole Diameter	1.83 mm [.072 in]
Wire Size	19 AWG
Mating Pin Diameter Range	.94 – 1.02 mm [.037 – .04 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Bag, Loose Piece
Packaging Quantity	2000

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-5331677-3
SOCKET,MIN-SPR SN SER-3U SER-3



TE Part # 1-332070-3
SOCKET,MIN-SPR W/H AU SER-4

Customers Also Bought



TE Part #EM7503-000
X4-2.5-0-SP-SM



TE Part #234472-E
SRCA 1,27 10 F 1 I2426 137 E1 094 1,07 T



TE Part #5-102617-1
06 MODII HDR DRRA SHRD LF




TE Part #2-330808-8
SOCKET,MIN-SPR AU SER-1



TE Part #1617146-4
JMGACD-12MW = M39016/18-040M



TE Part #1735446-3
2MM PITCH HPI POST HEADER, VERTICAL, 3P



TE Part #2302790-1
VERTRECCASSY,RIGHTEND,MULTIGIG RT3



TE Part #1624365-1
NTC0805 5% 5K0



Documents

Product Drawings

[SOCKET,MIN-SPR AU SER-4](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-332070-1_AA.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-332070-1_AA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-332070-1_AA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English