

Features

- M18 short housing
- IO-Link
- Sensitivity adjustment via IO-Link
- Polarizing filter
- Calibrated range
- Immunity to mutual interferences

RS PRO Photoelectric Sensor

RS Stock No.: 0360253



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- M18 short housing
- IO-Link
- Sensitivity adjustment via IO-Link
- Polarizing filter
- Calibrated range
- Immunity to mutual interferences

General Specifications

Detection Type	Reflex
Sensing/Detection Range	20...7'000 mm
Operating Distance	30...5'500 mm
Standard Sensing Object	Referenzreflektor LXR-0000-084
Light Source	Red LED
Diameter of the Light Spot	Ø 21 mm (1 m)/Ø 110 mm (6 m)
Sensing Distance Adjustment	'500...7'000 mm, IO-Link
Output Type	PNP / Output 1: Light-on/IO-Link, Output 2: Dark-on
Response Time	≤ 340 us (normal)/≤ 1 ms/≤ 115 us
Connection/Terminal Type	4-pin M12
Indicator	LED
Interface	IO-Link
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+65°C

Electrical Specifications

Operating Supply Voltage	10 ... 30 VDC
Current Consumption	≤ 200 mA
Voltage Drop	≤ (U _b -2.0 V)/approx. 0 V
Maximum Switching Frequency	≤ 4.5 kHz
Reverse Polarity Protection	YES
Overload Protection	YES
Short Circuit Protection	YES

Mechanical Specifications

Body Style	Barrel
Mounting Type	Screw
Housing Material	ABS
Lens/Face Material	PMMA
Dimensions	M18 x 37 mm
Width / Diameter	15 mm
Length	37 mm
Depth	M18
Weight	6 g
Shock Resistance	IEC 60947-5-2
Vibration Resistance	IEC 60947-5-2

Protection Category

IP Rating	IP67
-----------	------

Approvals

Compliance/Certifications	CE / CULus / ECOLAB
---------------------------	---------------------

