

Cleaner XGT®

CL002G

40Vmax • 210 mbar • 0,5 L

XGT® powered high-suction vacuum cleaner with One touch switch.

CL002G has 4-mode selection with memory function. Number of green lamp indicates the selected mode. Increased storage capacity for longer time between waste disposal.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	1,2 m³/min
Max. sealed suction	210 mbar
Suction power	20 / 45 / 70 / 125 W
Continuous use XGT® 40Vmax / 2.5 Ah	80 / 40 / 25 / 16 min
Continuous Use XGT® 40V Max / 4.0 Ah	128 / 64 / 40 / 25 min
Dust Bag Capacity	0,5 L
Sound Pressure Level (L _{pA})	54 / 59 / 62 / 65 dB (A)
Product net weight	1,1 kg
Tool weight with battery	1,8 - 3,0 kg
Product Dimensions (L x W x H):	1081 x 114 x 158 mm
Brushless Motor	✓

User benefits

- 4 modes with memory function
- Built-in LED light illuminates the work area
- Cleaning of tight places can be done without nozzle
- Increased storage capacity for longer time between waste disposal
- Ergonomic soft grip handle provides increased comfort
- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- Battery protection system automatically shuts off power when the battery level is low
- Quiet cleaning achieved by redesigning air flow structure

Link to product - www.makitauk.com



Related products

Optional AC

123539-7

Floor T-Nozzle 225 mm, Black

1910Y3-1

TELESCOPIC PIPE SET

191D77-1

Straight Pipe

458942-6

Suction Tube With Pipe Lock



140H95-0

Seat Nozzle, Ø32 Mm



191D73-9

Cyclone Pre-Separator 400 ml



191E30-3

Flexible Hose Set



Other

User manual

Parts drawing