

8245-180 JC

Combination pliers

Euro pattern

Code	ETIM
6733150	EC000836
EAN	UNSPSC
4010886673317	27-11-21-04
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



Article description

- Acc. to DIN ISO 5746
- Universal model with slimline head, ideal for confined spaces
- Induction-hardened precision cutting edges, hardness 62 - 64 HRC
- For round and flat material
- For medium-hard wire 1.6 mm
- GEDORE special hardened and tempered steel, drop-forged, oil-hardened and annealed
- JC = chrome-plated, with 2-component handle covers
- TL = steel-grey, with blue dipped non-slip handles
- TC = chrome-plated, with blue dipped handles

Article information

Contents (Qty of pieces)	1	Hardening process	Induction hardened
Net weight [kg]	0,28 kg	Joint types	inserted joint
Total length [mm]	180 mm	Hardness of cutting edge	62 - 64 HRC
Total width [mm]	53 mm	Jaw length L3 [mm]	38 mm
Total height [mm]	22 mm	Width of centres W4 [mm]	6,4 mm
Material	Heat-treated steel	Head thickness [mm] T1	9,8 mm
Standard	DIN ISO 5746	Handle colour	blue
Width of head l [mm]	27,0 mm	Bevel	with
Design non-sparking	No	Cutting values	Hard wire: 2,2 mm / 11 AWG Medium hard wire: 3,4 mm / 8 AWG Soft wire: 5 mm / 4 AWG Cu cable, multi wire cross section: 16 mm ² Multi-wire cable Ø: 12 mm
Handle design	2C	Blade shape	with facet
Baking mold	flat jaws		