

ASI SACB KABEL-ENDDICHTUNG - Seal



1692336

<https://www.phoenixcontact.com/gb/products/1692336>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End sealing for AS-Interface flat-ribbon conductor, can be used on both sides, color:Black



Commercial data

Item number	1692336
Packing unit	100 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	AF3ZAX
Product key	AF3ZAX
Catalog page	Page 284 (PC-2009)
GTIN	4017918446499
Weight per piece (including packing)	0.39 g
Weight per piece (excluding packing)	0.239 g
Customs tariff number	40169300
Country of origin	IT

ASI SACB KABEL-ENDDICHTUNG - Seal



1692336

<https://www.phoenixcontact.com/gb/products/1692336>

Technical data

Product properties

Product type	Seal
--------------	------

Material specifications

Seal material	TPE
---------------	-----

Cable/line

Other resistance	Resistant to ozone
Special properties	FDA compliant

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 110 °C (Seal)
---------------------------------	--------------------------

Standards and regulations


Other resistance	Resistant to ozone
------------------	--------------------

1692336

<https://www.phoenixcontact.com/gb/products/1692336>

Drawings

Dimensional drawing



1692336

<https://www.phoenixcontact.com/gb/products/1692336>

Classifications

ECLASS

ECLASS-13.0	27440192
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.145 kg CO2e