

# KERN EOE 300K100L



Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.



## Measuring system

Adjustment options:	External calibration
Linearity:	200 g
Readability [d]:	100 g
Recommended adjusting weight:	200 kg (M2)
Repeatability:	100 g
Resolution:	3000
Tare range:	300 kg
Warm up time:	10 min
Weighing capacity [Max]:	300 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

## Display

Display digit height:	2,500 cm
-----------------------	----------

## Functions

Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Battery:	4x1.5 V AA
Input voltage:	220 V - 240 V AC 50 Hz
Mains adapter/adapter included:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	100 h
-----------------	-------

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

## Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	615 x 615 x 80 mm
Gross weight:	15,200 kg
Net weight:	13,500 kg
Shipping method:	Parcel service

## Construction

Cable length of display device:	2,700 m
Casing material:	plastic
Dimensions of display device (WxDxH):	235 x 114 x 51 mm
Dimensions of weighing plate (WxDxH):	553 x 553 x 62 mm
Material weighing plate:	Steel lacquered
Wall mount:	yes
Weighing surface (WxD):	550 x 550 mm

## Piktogramme

### STANDARD



### OPTION

